



AMP-TWIST SLX Series Modular Jack, category 6A, shielded , 4 Pair, without dust cover, red

Product Classification

Portfolio	NETCONNECT®
Product Series	SLX Series
Product Type	Modular jack
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America

Dimensions

Compatible Cable Diameter, maximum	9.00 mm   0.35 in
Compatible Insulated Conductor Diameter, maximum	1.600 mm   0.063 in
Depth	36.80 mm   1.45 in
Height	16.13 mm   0.64 in
Width	14.44 mm   0.57 in

Electrical Specifications

ANSI/TIA Category	6A
Transmission Standard	ANSI/TIA-568-C.2   ISO/IEC 11801 Class EA

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Cable Type	F/FTP (shielded)   S/FTP (shielded)   S/STP (shielded)
Color	Red
Mount Type	Keystone faceplates and panels   SL Series faceplates and panels
Package Quantity	24
Packaging Type	Bag   Box
Panel Cutout, recommended	14.78 x 20.07 mm (0.58 x 0.79 in)
Panel Thickness, recommended	1.60 mm

Mechanical Specifications

Conductor Gauge, solid	26–22 AWG
Conductor Gauge, stranded	26–24 AWG
Conductor Type	Solid   Stranded
Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Contact Plating Thickness	1.27 µm
Material Type	Polycarbonate   ZMAC 5
Outlet Type	Standard
Termination Tool	SL Termination tool
Termination Type	IDC
Wiring	T568A   T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant