
KEYSTONE CAT6 JACK FOG WHITE, 25PK

OR-KT2J625 | [Ortronics](#)



FEATURES & BENEFITS

Resealable package of 25 Category 6 Keystone jack, 8-position, 180 degree exit, icon compatible, T568A/B wiring, Fog White. Keystone, KT2J jacks and modules feature New installer friendly lacing cap termination with free termination tool in every carton. The keystone footprint allows flexibility in installation scheduling because its rear insertion into the faceplate allows the technician to complete the termination before and during the construction process.

- **Meets Category 6 standard:** Ensures standards compliance.
 - **Easy lace wiring cap** reduces wiring time.
 - **Easy to follow universal wiring label:** Quick and user-friendly, eliminates confusion.
 - **Rear loading:** preferred mounting for panels.
 - **Icon compatible, C6 marking on jack face:** Supports 606 designation requirements.
 - **Free terminaiaon tool in each carton of 20 jacks** convenient no extra termination toolrequired .
-
- **RoHS compliant:** Lead free.
-
- **Resealable bag of 25KT2J jacks** : reduces prep time and packaging waste.

SPECIFICATIONS

GENERAL INFO

Color: Fog White
Footprint: Keystone
Number Of Ports: 1
UL Standards Tested: UL 1863
Product Series: Keystone TC2
Type: Jacks and Modules

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CUL Listing No: E131600
UL Standard: 1

CONSTRUCTION INFORMATION

Component 1: Plastic Jack Housing

Component 2: Array of eight modular contacts.

Component 3: Compact IDC contacts lower EMI

Component 4: Printed circuit board

Finish Plating 2: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area

Material 1: High Impact Thermoplastic PC 94V-0

Material 2: Beryllium copper

Material 3: Tin plated Phosphor bronze

Material 4: Two-sided FR-4 epoxy resin/glass base with solder mask

DIMENSIONS

Depth (Metric): 34.80 mm

Depth (US): 1.37"

Height (US): .88 "

Width (Metric): 15.95 mm

Width (US): .628 "

TECHNICAL INFORMATION

Category Rating: Cat 6 component compliant

Performance Rating: Cat6

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Exception

Note: Contact Customer Support for Buy American Act options

