



e-POI Subrack with Interface Card

Product Classification

Brand	Era™ ION®-E
Product Type	Subrack

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Rack Type	EIA 19 in

Mechanical Specifications

Mounting	Rack
Slots Available, quantity	8

Environmental Specifications

Mean Time Between Failures (MTBF)	146 yr @ 25 °C
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)

Dimensions

Depth	395.00 mm 15.55 in
Height	178.00 mm 7.01 in
Net Weight	7.70 kg 16.98 lb
Width	482.00 mm 18.98 in