



Fiber Optic Uniboot Patch Cord, Duplex, LC/UPC, multimode, OM4, LSZH, 3 m

- Patch cords using Uniboot technology combine, modularity, flexibility with easy mating and demating connectivity
- Uniboot connectors feature an adjustable polarity via a manual and independent rotation of each single connector body
- Uniboot technology features a push-pull mechanism operated by squeezing the connector boot
- Adjustable connector pitch between 5.25 and 6.25 mm

Product Classification

Portfolio	NETCONNECT®
Brand	Uniboot®
Product Series	Uniboot
Product Type	Fiber patch cord, duplex
Regional Availability	EMEA Latin America North America

Construction Materials

Fiber Type	OM4
Total Fibers, quantity	2
Jacket Color	Aqua
Fiber Mode	Multimode

Dimensions

Cord Length	3.00 m 9.84 ft
Diameter Over Jacket	1.50 mm 0.06 in
Ordering Note	Total connector length from tip to boot is 63.5 mm (2.5 in)

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing

General Specifications

Interface, connector A	LC/UPC
Interface, connector B	LC/UPC
Color, boot A	Aqua
Color, boot B	Aqua
Color, connector A	Beige

Color, connector B	Beige
Connector A, quantity	2
Connector B, quantity	2
Package Quantity	6
Polarity	Adjustable Universal
Transmission Standards	IEC 61300-3-4 method B
Interface Feature, connector A	Uniboot
Interface Feature, connector B	Uniboot

Optical Performance

Insertion Loss, maximum, connector A	0.15 dB
Insertion Loss, maximum, connector B	0.15 dB
Return Loss, minimum, connector A	35.00 dB
Return Loss, minimum, connector B	35.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant