



Fiber Optic Patch Cord, LC to LC, OM3, twin zip, 2 m, aqua

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber patch cord, duplex
Regional Availability	Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM3
Total Fibers, quantity	2
Jacket Color	Aqua
Fiber Mode	Multimode

Dimensions

Cord Length	2.00 m 6.56 ft
Diameter Over Jacket	1.80 mm 0.07 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
---------------------	-------------------------------

General Specifications

Interface, connector A	LC/UPC
Interface, connector B	LC/UPC
Color, boot A	Beige
Color, boot B	Beige
Color, connector A	Beige
Color, connector B	Beige
Connector A, quantity	2
Connector B, quantity	2
Package Quantity	1
Polarity	Pairs, flipped

Optical Performance

Insertion Loss, maximum, connector A 0.30 dB

Insertion Loss, maximum, connector B 0.30 dB

Return Loss, minimum, connector A 30.00 dB

Return Loss, minimum, connector B 30.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant