



Quality Products. Service Excellence.

100-240 VAC / 10A IEC Heavy Duty Outlet Strip 1581 Series

Features



- Rated 100-240 VAC, 10 A, 50/60 Hz and designed for use with IEC power cords
- All metal housing – tough extruded aluminum case with black powder-coated steel cover.
- On-Off switch is rocker type with green light (on those units with on-off switch - listed below) or a green pilot light to indicate power on.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.

Specifications

- One IEC 320 - C14 inlet, and 4, 5, 6 or 8 IEC 320 - C13 outlets.
- Includes 10A circuit breaker to prevent accidental line overload.
- cULus listed to UL 60950-1 (2nd Edition); Amd1 + Amd2, and CAN/CSA C22.2 No. 60950-1-07 (2nd Edition); Amd1 + Amd2.
- TÜV certified to EN 60950-1:2006/A2:2013-09, and IEC 60950-1 (ed.2); am1;am2
- CE compliant to the European Low Voltage Directive 2014/35/EU.



Accessories

- Rack Cabinet Vertical Mount Adaptor
- Input Accessory Cords

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Outlet Qty	Outlet Type	Inlet Type
		Height	Width	Length			
1581H4	1581T4	2.33	2.13	10.18	4	C13	C14
1581H5	1581T5	2.33	2.13	11.75	5	C13	C14
1581H6	1581T6	2.33	2.13	13.36	6	C13	C14
1581H8	1581T8	2.33	2.13	16.51	8	C13	C14

Data subject to change without notice

© 2018. Hammond Manufacturing Ltd. All rights reserved.