



*Quality Products. Service Excellence.*

## Adjustable Depth Hinged Wall Rack *APB Series*

Rugged 100 lbs Weight Capacity

### Features



- Constructed in 14-gauge steel.
- EIA-310-D compliant 10-32 tapped rails with 19" mounting.
- Hinged for easy rear access.
- Rack unit indicators help with installation.
- Adjustable depth from 12" to 18" using slots for easy set-up and adjusting.
- Rear cable access with multiple tie points for cable management.
- Finished in smooth black powder paint.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Includes starter pack of mounting hardware. (25-pack of 10-32 screws)
- Tested to nearly double the suggested load rating of 100 lbs (45.36 kg).
- Swing weight is rated for 1.5 lbs (0.68 kg) per rack unit, evenly distributed.
- TAA Compliant.
- RoHS Compliant.
- Manufactured in North America.

### Similar Products

- If you are looking for a taller or deeper option, consider the **HWMR** Series.
- If you are looking for an APB with a shelf included, consider the **APBS** Series.

### Gallery



### Accessories

- Universal Rack Shelf
- Outlet Strips
- Cable Management
- 10-32 Mounting Hardware
- Two Post Mounting Keyboard & Equipment Shelf
- Rack Panels
- Mounting Hardware
- Hook and Loop Roll

Part No.	Overall Dimensions		Rack Units	Mounting Dimensions			
	Height	Width		Height	Width	Min Depth	Max Depth
APB19007BK1	6.98	19.25	4U	7.00	19.00	12.00	18.00
APB19010BK1	10.48	19.25	6U	10.50	19.00	12.00	18.00
APB19014BK1	13.98	19.25	8U	14.00	19.00	12.00	18.00
APB19021BK1	20.98	19.25	12U	21.00	19.00	12.00	18.00

