

Bells

Vibrating

156G Series

Edwards 156G Series bells are self-contained underdome monitor bells. These grounded, vibrating bells are insulated, and have a concealed plunger. They are also suitable for AC powered security systems.

Features and Specifications

- 3", 4" and 6" gong sizes
- Corrosion resistant gray finish
- Supplied with gasket for outdoor applications
- Low current draw permits long wire runs
- Mounts on 3 3/4" (95mm) bolt circle



Ordering Information					
Description	Cat. No.	Operating Voltage	Current	Gong Size	dB at 1m/10ft.
AC	156G-3G5	24V AC	0.30 A	3" (76mm)	82/72
	156G-4G5	24V AC	0.30 A	4" (102mm)	86/76
	156G-6G5	24V AC	0.30 A	6" (152mm)	90/80
DC	156G-3AX	12-18V DC	0.20 A	3" (76mm)	82/72
	156G-6AW	20-24V DC	0.15 A	6" (152mm)	90/80
	156G-3G1	24V DC	0.15 A	3" (76mm)	82/72
	156G-4G1	24V DC	0.15 A	4" (102mm)	86/76
	156G-6G1	24V DC	0.15 A	6" (152mm)	90/80
	156G-3J1	32V DC	0.11 A	3" (76mm)	82/72
AC/DC	156G-3AM	6-8V DC 8-10V AC	0.80 A	3" (76mm)	82/72
	156G-4AM	6-8V DC 8-10V AC	0.80 A	4" (102mm)	86/76
	156G-6AM	6-8V DC 8-10V AC	0.80 A	6" (152mm)	90/80

Weights and Dimensions				
Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)	Dimensions	
			A	B
156G-3AM	0.86	0.98	3" (76mm)	1 7/8" (48mm)
156G-3AX	0.86	0.98	3" (76mm)	1 7/8" (48mm)
156G-3G1	0.86	0.98	3" (76mm)	1 7/8" (48mm)
156G-3G5	0.86	0.98	3" (76mm)	1 7/8" (48mm)
156G-3J1	0.86	0.98	3" (76mm)	1 7/8" (48mm)
156G-4AM	1.33	1.53	4" (102mm)	1 7/8" (48mm)
156G-4G1	1.33	1.53	4" (102mm)	1 7/8" (48mm)
156G-4G5	1.33	1.53	4" (102mm)	1 7/8" (48mm)
156G-6AM	1.82	2.10	6" (152mm)	2 5/16" (59mm)
156G-6AW	1.82	2.10	6" (152mm)	2 5/16" (59mm)
156G-6G1	1.82	2.10	6" (152mm)	2 5/16" (59mm)
156G-6G5	1.82	2.10	6" (152mm)	2 5/16" (59mm)

