

Rolling Ball Switches

Low Voltage

44, 45 and 46E

The 44, 45 and 46E rolling ball switches are insulated, rugged devices that operate from pressure in any direction. Installation requires no mortise.

Features and Specifications

- Fast installation
- Low voltage
- Insulated



Ordering Information		Current		
Description	Cat. No.	Operating Voltage	DC Current	AC Current
Push to Open	44	12V	2 A	2 A
		24V	1 A	2 A
		48V	0.5 A	1 A
Push to Close	45	12V	2 A	2 A
		24V	1 A	2 A
		48V	0.5 A	1 A
Push to Make, then Break and Repeat on Return	46E	12V	2 A	2 A
		24V	1 A	2 A
		48V	0.5 A	1 A

Weights and Dimensions			
Cat. No.	Approx. Shipping Weight (lb.)	Hole Diameter (in.)	Hole Depth (in.)
44	0.10	13/16	1 1/8
45	0.10	13/16	1 1/8
46E	0.10	13/16	1 1/8

