



Powering Business Worldwide

pe.eaton.com

FNQ-R Limitron

FNQ-R-3

UPC:051712147088

Dimensions:

- **Height:** 1.5 IN
- **Length:** .41 IN
- **Width:** .41 IN

Weight: .15 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Current-limiting, high inrush, time delay
- **Special Features:** Rejection style
- **Application:** Line protection, small control transformers, industrial control, branch circuits
- **Amperage Rating:** 3A
- **Voltage Rating:** 600V
- **Interrupt Rating:** 200 kAIC
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Response Time:** 12s at 200%
- **Diameter:** .40625 IN
- **Material:** Melamine tube
- **Class:** Class CC
- **Connection:** Ferrule end X ferrule end

Supporting documents:

- [Product Catalog](#)
- [CLASS CC TIME DELAY](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant



