

# Surface Downlight 10W

Cylindrical surface mounted LED downlight

- Stylish design ideal for contemporary commercial applications
- Quick and simple surface mount installation
- Available in black and white finishes
- Triac dimmable as standard



**NEW**

New product  
for 2018



3 year  
ext. warranty\*



60°  
beam angle



Dimmable  
as standard



✓ JC84301BLK

## Classification

⚡ Class 1  
IP54 | 240V

## LED

3000K | CRI: Ra (80)  
4000K | CRI: Ra (80)


## Finishes

Black (**BLK**), White (**WH**)

## Construction

Body: Aluminium  
Lens: Glass

JC84300 / JC84301



All data sheets and installation sheets  
available at [jcc.co.uk](http://jcc.co.uk)

Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC84301	Surface Downlight	3000K	Yes	10W	800	80
JC84300	Surface Downlight	4000K	Yes	10W	950	95

For Black add **BLK** suffix, for White add **WH** suffix.

\*Requires online registration.