



New product  
for 2018



3 year  
ext. warranty\*



60°  
beam angle



Dimmable  
as standard



JC84303BLK

#### Classification

⚡ Class 1  
IP54 | 240V

#### LED

3000K | CRI: Ra (80)  
4000K | CRI: Ra (80)



#### Finishes

Black (**BLK**), White (**WH**)

#### Construction

Body: Aluminium  
Lens: Glass

JC84302 / JC84303



All data sheets and installation sheets  
available at [jcc.co.uk](http://jcc.co.uk)

# Surface Downlight 25W

## Cylindrical surface mounted LED downlight

- Stylish design ideal for contemporary commercial applications
- Quick and simple surface mount installation
- Available in black and white finishes
- Triac dimmable as standard



Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC84303	Surface Downlight	3000K	Yes	25W	2540	102
JC84302	Surface Downlight	4000K	Yes	25W	2910	116

For Black add **BLK** suffix, for White add **WH** suffix.

\*Requires online registration.