


# ToughLED™ Weatherproof 4ft


## Efficient, highly durable batten

- Ultra efficient, up to 128 lumens per circuit Watt
- Stainless steel anti-tamper clips
- Polycarbonate diffuser, ABS body, suitable for food preparation areas
- Press-fit terminals, loop in loop out for quick and simple installation
- Available with white opal or frosted diffuser

**NEW** New product for 2018

 3 year ext. warranty\*


 120° beam angle

 Sensing options available

 Emergency options available



### Classification

 Class 1  
IP65 | 240V

### LED

4000K | CRI: Ra (80)

### Finishes

Grey

### Construction


Body: ABS  
Diffuser: Polycarbonate

Code	Description	Col temp.	Dim.	Watt	Lumens (FR)	Lumens (WOP)
JC71553	Weatherproof 4ft single	4000K	No	18W	2300	2050
JC71553MW	Weatherproof 4ft single m/w on/off	4000K	No	18W	2300	2050
JC71553EM	Weatherproof 4ft single emerg.	4000K	No	18W	2300	2050
JC71553MWEM	Weatherproof 4ft single m/w on/off em.	4000K	No	18W	2300	2050
JC71554	Weatherproof 4ft twin	4000K	No	37W	4700	4300
JC71554MW	Weatherproof 4ft twin m/w on/off	4000K	No	37W	4700	4300
JC71554EM	Weatherproof 4ft twin emerg.	4000K	No	37W	4700	4300
JC71554MWEM	Weatherproof 4ft twin m/w on/off em.	4000K	No	37W	4700	4300

For Frosted Diffuser add **FR** suffix, for White Opal Diffuser add **WOP** suffix.

\*Requires online registration.

### Classification

 Class 1  
IP65 | 240V

### LED

4000K | CRI: Ra (80)

### Finishes

Grey

### Construction

Body: ABS  
Diffuser: Polycarbonate

### JC71553 / JC71554



All data sheets and installation sheets available at [jcc.co.uk](http://jcc.co.uk)