

# ToughLED™ Weatherproof 6ft

## Efficient, highly durable batten

- Ultra efficient, up to 123 lumens per circuit Watt
- Stainless steel anti-tamper clips
- Polycarbonate diffuser, ABS body, suitable for food preparation areas
- Press-fit terminals, loop in loop out for quick and simple installation
- Available with white opal or frosted diffuser

**NEW**

New product for 2018



3 year ext. warranty\*



120° beam angle



Sensing options available



Emergency options available



### Classification

⊕ Class 1  
IP65 | 240V

### LED

4000K | CRI: Ra (80)

### Finishes

Grey

### Construction

Body: ABS  
Diffuser: Polycarbonate

### JC71557 / JC71558

85mm 118mm  
| 80mm



Code	Description	Col temp.	Dim.	Watt	Lumens (FR)	Lumens (WOP)
JC71557	Weatherproof 6ft single	4000K	No	35W	4300	3800
JC71557MW	Weatherproof 6ft single m/w on/off	4000K	No	35W	4300	3800
JC71557EM	Weatherproof 6ft single emerg.	4000K	No	35W	4300	3800
JC71557MWEM	Weatherproof 6ft single m/w on/off em.	4000K	No	35W	4300	3800
JC71558	Weatherproof 6ft twin	4000K	No	70W	8600	7100
JC71558MW	Weatherproof 6ft twin m/w on/off	4000K	No	70W	8600	7100
JC71558EM	Weatherproof 6ft twin emerg.	4000K	No	70W	8600	7100
JC71558MWEM	Weatherproof 6ft twin m/w on/off em.	4000K	No	70W	8600	7100

For Frosted Diffuser add **FR** suffix, for White Opal Diffuser add **WOP** suffix.

\*Requires online registration.