

Starscoop™ 20W

Commercial LED display light

- Highly efficient, 101 lumens per circuit Watt
- Zero maintenance, no need to relamp
- Available in white and black finishes
- Durable die cast aluminium construction
- 350° rotatable and 35° tiltable

✓ JC47441WH




✓ JC47441BLK





NEW New product for 2018

 3 year ext. warranty*

 36° beam angle

 Emergency options available

Classification

 Class 2
 Class 1 (EM00172)
 IP20 | 240V

LED

4000K | CRI: Ra (80)

Finishes

Black (**BLK**), White (**WH**)


Construction

Body: Aluminium
 Lens: Glass


Installation

Cut out Ø: 120-130mm

JC47441



Ø145mm



Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
------	-------------	-----------	------	------	--------	------

JC47441	Starscoop	4000K	No	20W	2020	101
---------	-----------	-------	----	-----	------	-----

EM00172	Plug and Play Emergency Pack	-	-	-	-	-
---------	------------------------------	---	---	---	---	---

For Black add **BLK** suffix, for White add **WH** suffix.

*Requires online registration.

All data sheets and installation sheets available at jcc.co.uk