


Starspot™ 600 Track Kit

High performance LED spotlights

NEW New product for 2018

 5 year ext. warranty*

 36° beam angle


 Dimmable as standard

- Track kit includes: 3 x Starspot 600 spotlights, 1120mm track section and 86mm live end
- 20% greater light output than 50W GU10 halogen
- Over 80% energy saving against halogen
- Zero maintenance, no need to relamp
- Triac dimmable as standard



∧ JC14224BLK

Classification

 Class 1
IP20 | 240V

LED

3000K | CRI: Ra (85)
4000K | CRI: Ra (85)

Finishes

Black (BLK), White (WH)


Construction

Body: Aluminium
Lens: Polycarbonate

Installation

Method of fix: Surface Mounted

JC14224 / JC14225



All data sheets and installation sheets available at jcc.co.uk

✓ JC14222WH



Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC14224	Starspot 600 Track Kit	3000K	Yes	7W	580	83
JC14225	Starspot 600 Track Kit	4000K	Yes	7W	600	86

For Black add **BLK** suffix, for White add **WH** suffix.

*Requires online registration.