

# 5m LED Strip Reel

## High output LED Strip

- 75W driver for medium output strip and 100W driver for high output strip
- 5m lengths as standard (10mm wide)
- Cuttable and connectable
- Available in warm and cool white colour temperatures
- Dimmable variants available
- High output strip variants require aluminium profile
- Self adhesive



5 year  
ext. warranty\*



Dimmable  
options available



### Classification

Class 2 (Driver)

Class 3 (Strip)

IP65 (Strip) IP20 (driver) | 240V

### LED

3000K | CRI: Ra (85)

4000K | CRI: Ra (85)

### Accessories

Linkable extrusions and  
accessories available (see p.189)

Code	Description	Col temp.	Dim.	Watt (pm)	Lumens (pm)	LpcW
JC83201	Low Output LED Strip & Dim. Driver	3000K	Yes	5.2W	500	96
JC83202	Low Output LED Strip & Dim. Driver	4000K	Yes	5.2W	500	96
JC83203	Medium Output LED Strip	3000K	No	13W	1100	84
JC83204	Medium Output LED Strip	4000K	No	13W	1100	84
JC83205	High Output LED Strip	3000K	No	20W	1700	85
JC83206	High Output LED Strip	4000K	No	20W	1700	85
JC83208	LED Driver IP20	-	No	75W	-	-
JC83208DIM	LED Driver IP65 - 1-10V	-	Yes	75W	-	-
JC83209	LED Driver IP20	-	No	100W	-	-
JC83209DIM	LED Driver IP65 - 1-10V	-	Yes	100W	-	-

\*Requires online registration.

All data sheets and installation sheets  
available at [jcc.co.uk](http://jcc.co.uk)