

RadiaLED® Utility 12W


Direct 28W 2D replacements

- IP65 weather resistant
- Anti-vandal construction
- Corrosion resistant, suitable for coastal locations
- Opal or prismatic polycarbonate diffuser options
- Dusk to dawn on/off photocell options available
- Up to 95 lumens per circuit Watt

✓ JC23401WPR




 5 year ext. warranty*

 Sensing options available

 Emergency options available

Classification

 Class 1
IP65 | 240V

LED

4000K | CRI: Ra (80)


Finishes

White Opal (**WOP**),
White Prismatic (**WPR**)

Construction

Body: Polycarbonate
Diffuser: Polycarbonate

JC23401



85mm Ø205mm

Code	Description	Col temp.	Dim.	Watt	Lumens (WOP)	Lumens (WPR)
JC23401	RadiaLED Utility	4000K	No	12W	700	1150
JC23431	RadiaLED Utility on/off photocell	4000K	No	12W	700	1150
JC23411	RadiaLED Utility microwave on/off	4000K	No	12W	700	1150
JC23421	RadiaLED Utility microwave dimming	4000K	-	12W	700	1150
JC23401EM	RadiaLED Utility emergency	4000K	No	12W	700	1150
JC23431EM	RadiaLED Utility on/off photocell em.	4000K	No	12W	700	1150
JC23411EM	RadiaLED Utility microwave on/off em.	4000K	No	12W	700	1150

For White Opal add **WOP** suffix, for White Prismatic add **WPR** suffix.

*Requires online registration.

All data sheets and installation sheets available at jcc.co.uk