



New product
for 2018



3 year
ext. warranty*



4 directional light



Matching bollard available,
see p.287

Classification

Class 1
IP54 | 240V

LED

3000K | CRI: Ra (80)


Finishes

Anthracite

Construction

Body: Aluminium
Diffuser: Polycarbonate

JC17019



All data sheets and installation sheets
available at jcc.co.uk

Wall Light

Architectural exterior LED lighting

- Durable die-cast aluminium construction
- IP54 protection against dust and moisture
- Stylish, contemporary design
- LED wall light with matching colour temperature and finish to the Architectural Exterior range



Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC17019	Wall Light	3000K	No	7W	423	60

*Requires online registration.