

Toughflood™ High Output


Ultra efficient 200W directional floodlight

- Up to 143 Lumens per circuit Watt
- 5 different beam angle options available
- LED modules can be adjusted individually
- IP66 weather resistance
- Features 10KV Surge protector as standard
- Produced to order, contact JCC customer services on **01243 838999**




NEW New product for 2018

 5 year ext. warranty*

 Multiple lens options available

 Produced to order call 01243 838999

Classification

 Class 1
IP66 | 240V
IK10

LED

4000K | CRI: Ra (70)

Finishes

Black

Construction

Body: Aluminium
Lens: Polycarbonate
Bracket: Galvanised steel

JC45222



Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC45222/30	Toughflood 30° Symmetric	4000K	No	200W	28,100	141
JC45222/45	Toughflood 45° Symmetric	4000K	No	200W	28,100	141
JC45222/70	Toughflood 70° Symmetric	4000K	No	200W	28,100	141
JC45222/711	Toughflood 70x110° Symmetric	4000K	No	200W	28,400	142
JC45222/613	Toughflood 60x130° Asymmetric	4000K	No	200W	28,500	143

Produced to order, contact JCC customer services on **01243 838999**.

*Requires online registration.

All data sheets and installation sheets available at jcc.co.uk