



2 year product guarantee

NiteLED™ Dome Bollard

Low wattage LED exterior lighting

- Direct 42W halogen GLS replacement
- Zero maintenance, no need to relamp
- Instant start up, no warm up time



Matching wall light available, see p.253

Classification

Class 1
IP44 | 240V

LED

4000K | CRI: Ra (80)

Finishes

Stainless steel (**SS**), for Black (**BLK**) see p.299

Construction


Body: Steel
Diffuser: Polycarbonate

Accessories

Root mounting kit (JC39224)

JC39224

Ø170mm



JC39423SS

Ø155mm



JC39422SS

Ø155mm



Ø166mm

Ø166mm



Code	Description	Col temp.	Dim.	Watt	Lumens	LpcW
JC39422SS	Short (475mm)	4000K	No	8.5W	200	24
JC39423SS	Medium (775mm)	4000K	No	8.5W	200	24
JC39224	Root mounting kit	-	-	-	-	-