

APC Back-UPS[®] 350

Best Value Battery Backup & Protection for Home and Home Office Computers

APC's Back-UPS provides enough battery backup power so you can work through short length power outages. It also safeguards your equipment against damaging surges and spikes that travel along utility and phone lines. The Back-UPS series is also "greener" than ever, using an ultra-efficient design that consumes less power during normal operation than any other battery backup in its class, saving you money on your electricity bill. Coupled with all the standard features of the Back-UPS series, the 350 is the perfect unit to protect your productivity from the constant threat of bad power and lost data.



Product Features:

- 1** **4 "Battery Backup & Surge Protected" Outlets** keep a CPU, monitor and other critical devices running when the power goes out or fluctuates outside safe levels.
- 2** **3 "Surge Only" Outlets** provide surge protection for your non-critical devices.
- 3** **Data Line Surge Protection** guards against surges and spikes traveling over an analog phone line (phone, fax, modem, DSL).
- 4** **Combination Power Button/LED Indicator** provides visual and audible status of unit.
- 5** **An ultra efficient electrical design**, RoHS compliance and use of all recyclable packaging materials minimize impact on the environment and maximize efficiency.
- 6** **Building Wiring Fault Indicator** lets you know if there are problems in your building's wiring.
- 7** **Push Button Circuit Breaker** enables quick recovery from overloads.
- 8** **Automatic Diagnostic Testing** ensures your unit is ready when you need it.
- 9** **3 yr Warranty, \$75,000 Equipment Protection Policy**, free technical phone and online support

Back-UPS 350 Specifications

Model Number	BE350G
Output	
Output Capacity	350 VA / 210 Watts
Output Voltage / Frequency (On utility)	120V / 60Hz
Output Voltage / Frequency (On battery)	115V +/-8%, 60 Hz +/-3Hz
Output Connections	6 total NEMA 5-15R outlets: 3 battery backup & surge 3 surge protection only
Waveform Type	Stepped Approximation to Sine Wave
Input	
Input Voltage / Frequency	120V / 60 Hz +/-1 Hz
Input Connection	5 ft cord with right angle plug (NEMA 5-15P)
Surge Protection	
AC Power Surge Protection	All outlets
Data Line Surge Protection	Analog phone line, RJ-11 (single line, 2-wire). For phone, fax, modem, DSL
Physical	
Unit Dimensions (H x W x D)	3.5" x 6.25" x 11.0"
Unit Weight	8.0 lbs
Shipping Dimensions (H x W x D)	5.0" x 7.75" x 14.25"
Shipping Weight	9.6 lbs
Color	Black
UPC Code	731304258902
Battery	
Battery Type	Maintenance-free, sealed lead-acid battery, leakproof
Management	
Alarms	Visual (LED) and audible alarms
Auto-Shutdown Software	None
Safety	
Certification/Approvals	cUL Listed, FCC Part 15 Class B, FCC Part 68, NOM, UL 1778, UL 497A, UL 498

APC by Schneider Electric

132 Fairgrounds Rd
West Kingston, RI 02892
Tel: 800-800-4272
www.apc.com

