

NetShelter AV Enclosures

Schneider Electric NetShelter SX Enclosures,
AV accessories, and Rack Cooling Products
for the professional AV industry



CONDUIT AND CABLE ACCESS ROOF

- > Four removable conduit access panels with holes varying in size and two cable access slots with brush strips for air containment
- > Two spring loaded pins allow for easy roof removal and installation with cables in place



EASILY ADJUSTABLE 10/32 THREADED VERTICAL MOUNTING RAILS WITH BUSBAR ATTACHMENT POINTS

- > To align, match the shapes along the side brace to the visible shapes shown through the opposite rail
- > Simple screw and cam engagement with captive screws
- > Easily align rails and adjust in 1/4 inch increments
- > Toollessly mount busbars
- > Numbered U positions



REMOVABLE SIDE PANELS AND FRONT/REAR DOORS

- > Half height side panels for easy and safe handling
- > Quick release latch on side panels
- > Lockable – same key for doors/side panels
- > Enclosure width the same with or without sides installed
- > Perforated front and rear doors
- > Split rear doors for better clearance in aisle



VERTICAL 0U ACCESSORY CHANNEL

- > Toollessly mount cable management accessories or directly fasten cable bundles
- > Toollessly mount power distribution
- > Toollessly mount busbars



CASTORS AND ADJUSTABLE LEVELLING FEET

- > Both are pre-installed and standard on all enclosures
- > Levelling feet easily adjustable from the top down



- > Static Load Capacity 3,000 lb
- > Doors, sides, roof, and rails are bonded to frame

Enclosures	SKU Number
42U 600mm Wide x 825mm Deep Enclosure with Sides and 10-32 Threaded Rails	AR3810
42U 600mm Wide x 825mm Deep Enclosure without Sides/Roof/Doors, includes 10-32 Threaded Rails	AR3812
24U 600mm Wide x 825mm Deep Enclosure with Sides and 10-32 Threaded Rails	AR3814

Related Products and Accessories

AV Power Options

Description	SKU Number
AV 15 Amp G Type Rack Power Filter, 120 V	G5BLK
AV Black 1kVA H Type Power Conditioner 120V	H10BLK
AV Black 1.5kVA H Type Power Conditioner 120V	H15BLK
AV Black 1kVA S Type Power Conditioner with Battery Backup 120V	S10BLK
AV Black 1.5 kVA S Type Power Conditioner with Battery Backup 120 V	S15BLK
AV Black Network Manageable 1.25 kW S Type Power Conditioner with Battery Backup 120V	S20BLK
AV Black S Type Extended Battery Pack 48Vdc	SBATTBLK



Rack Power Distribution

Description	SKU Number
Rack PDU, Switched, Zero U, 20 A, 120 V, (24) 5-20	AP7930
Rack PDU, Basic, Zero U, 20 A, 120 V, (24) 5-20	AP7530
Rack PDU, Basic, 1U, 20 A, 120 V, (10) 5-20; L5-20 P	AP9564



Cable Management

Description	SKU Number
Top Mount Conduit Access Adapter	AR7215
Horizontal cable manager, 2U with Cover, Plastic Fingers	AR8600A
Horizontal cable organizer, 1U, Cable Rings	AR8425A
Horizontal cable organizer, 2U, Cable Rings	AR8426A



Rack Cooling and Enclosure Accessories

Description	SKU Number
NetShelter AV 2U Rack Fan Panel	ACF600
NetShelter AV Rack Fan Temperature Controller	ACF601
2U Vent Panel with Temperature Display	ACAC40000
2U Vent Panel	ACAC40001
Adjustable Mounting Shelf 18 – 25"	AR8125
20 U Copper Busbar Attachment Kit	AR8395
Blanking Panel Kit 19" Black (1U, 2U, 4U, 8U) Black	AR8101BLK
#10-32 Hardware kit (Qty-36)	AR8005

