

Optolinx FCU-2805SFP

10/100/1000BaseT to 1000BaseSX/LX SFP Gigabit Media Converter



Features

- ▶ Complies with IEEE 802.3, 802.3u, 802.3ab, 802.3z
- ▶ Mini-GBIC SFP Connector
- ▶ IEEE 802.3x Full-Duplex Flow-Control & Back-Pressure in Half-Duplex
- ▶ Supports Auto MDI/MDI-X function
- ▶ Store-and-Forward mechanism
- ▶ Non-blocking full wire-speed forwarding rate
- ▶ Compact size for easy installation

Specifications

Standard

IEEE 802.3 10BaseT
IEEE 802.3u 100BaseTX
IEEE 802.3ab 1000BaseT
IEEE 802.3z 1000BaseSX/LX

Interface

1 x 1000BaseT RJ-45 Port (Auto-MDI/MDI-X) Twisted Pair
1 x 10/100/1000BaseT Port
1 x 1000BaseSX/LX Port

Data Transfer Rate

TP: 10/20Mbps for Half/Full-Duplex
100/200Mbps for Half/Full-Duplex
2000Mbps for Full-Duplex
Fiber: 2000Mbps for Full-Duplex

Fiber Connector

SFP Connector

LED

Power, TP Link/ACT, Fiber Link/ACT

DIP Switch

LFP Function (Disable/Enable) Setting

Power

5V DC, 2A

Power Consumption

5 Watts Max. / 17 BTU Max

Operation Temperature

0° C to 50° C (32° F to 122° F)

Storage Temperature

-10° C to 70° C (14° F to 158° F)

Operation Humidity

5% to 90% (Non-condensing)

Case Dimension (W x D x H)

97 x 70 x 26mm

Emission/Safety

FCC Class A, CE Class A

Warranty

2-Year Warranty

Ordering Information

FCU-2805SFP

10/100/1000BaseT to 1000BaseSX/LX Gigabit Media Converter, SFP