



## VIA Connect PRO

Wireless Presentation and Collaboration Solution

| HDMI | Ethernet - RJ-45



VIA Connect PRO is a wireless collaboration and presentation solution that makes sharing and presenting in meetings easier. With any laptop or mobile device, users can view, edit and comment on documents in real time, share files and chat with individuals or multiple participants simultaneously. The solution can show up to four screens on the main display. From any laptop or mobile device, students, teachers or any in-room meeting participant can view the main display, edit documents together in real time, share any size file, turn the main display into a digital whiteboard, and more. The solution features iOS mirroring for MacBook, iPad, iPhone, Windows phone and Android mirroring (Lollipop OS 5.0 or newer). VIA Connect PRO is ideal for huddle rooms, offering the best price-performance in the market

### FEATURES

**60fps Streaming Multimedia** - Share HD wireless video streaming (using the VIA app Multimedia feature)

**Wireless Connection for up to 254 Devices** - Utilizing Compatible External Wireless Network iOS and Android Mirroring

**Wireless Device Connectivity** - No dongle needed  
DHCP Support

**Graphic Output Formats** - Outputs to either an HDMI or Mini DisplayPort display. Note: Does not support graphic output to both the HDMI and Mini Display Port simultaneously

**Cloud-Based File Sharing** - Drag and drop files to the internal VIA cloud storage (32GB)  
Whiteboard Support

**Control** - Give a participant control over a presenter's PC for true collaboration

**Chat** - Send an instant message to another user

iCloud Integration

Seamless Integration with VIA Site Management (VSM) Software & the VIA Pad

Multilingual Support - Experience VIA in your language

Warranty - 3-years on hardware



# KRAMER

## TECHNICAL SPECIFICATIONS

---

INPUTS:	4 USB 3.0, 1 LAN on an RJ-45 connector
GRAPHIC OUTPUTS:	1 HDMI, 1 mini DisplayPort. Note: Does not support graphic output to both the HDMI and Mini Display Port simultaneously
AUDIO OUTPUT:	1 3.5mm mini jack for headphones/speakers
PROCESSOR:	4th generation Intel® Dual core 1.4GHz
MAIN MEMORY:	4GB, high speed
STORAGE:	32GB, solid-state drive
LAN:	Gigabit LAN
AUDIO:	Analog or embedded HDMI, S/PDIF Realtek ALC269
POWER SUPPLY:	65W power adapter (19V, 3.4A)
INPUT VOLTAGE:	100V~220V AC, 50/60Hz, auto sensing
INCLUDED ACCESSORIES:	Power cord, Kramer mini DP to VGA adapter, VESA mounting bracket
PRODUCT DIMENSION:	11.80cm x 11.50cm x 4.00cm (4.65" x 4.53" x 1.57" ) W, D, H
PRODUCT WEIGHT:	0.5kg (1.1lbs) approx
SHIPPING DIMENSION:	23.20cm x 13.60cm x 10.00cm (9.13" x 5.35" x 3.94" ) W, D, H
SHIPPING WEIGHT:	1.0kg (2.2lbs) approx



# KRAMER

## CONFIGURATIONS

VIA Connect PRO    Wireless Presentation and Collaboration Solution

VIA Digital Signage Module    License for Dynamic Content Display Feature Module

