



GREENLEE®

MADE FOR THE TRADE!™

MOBILE BENDING

881 MBT (MOBILE BENDING TABLE)

**ONE-TIME SET UP
COMPLETE MOBILITY
ON-BOARD STORAGE**

881 Mobile Bending Table

Conduit bending with Greenlee's 881 Bender has gone mobile. Introducing the Mobile Bending Table, Greenlee's newest bending innovation. It's a patent pending, all-in-one bending solution that gives operators the power and performance of the popular 881 Bender on a wheeled table. It is quick to set up, stores all components for the 881 Bender and can wheel around the jobsite with ease – saving crews nearly an hour with every move.

**ONE-TIME SET UP
SAVE ONE HOUR
WITH EVERY MOVE!**



Whether you already own an 881 Bender or are purchasing the bender and table together, the entire unit is **RUGGED**, **FEATURE-RICH** and **DESIGNED** to get each job done faster, safer and easier. Just wheel it into position, plug it in and start bending.

- 1 Two sticks of IMC conduit included so you can use the MBT right away
- 2 Locking swivel wheels for maneuverability when you want to move it, and staying power when you don't
- 3 Fork pockets so you can conveniently move the unit with a fork truck
- 4 Ram positioner to ease the set up of the Ram to accommodate different size shoes
- 5 Steel pegs with hitch pins for storage of shoes and saddles
- 6 Carriage assembly so you can mount the 881 Bender Unit directly to the MBT
- 7 Vice-chain to hold conduit securely for accurate bends – prevents conduit from twisting or turning during bend
- 8 Pump basket holds the hydraulic pump for the 881 Bender Unit
- 9 Storage for follow bars

881 MBT

COMPLETE MOBILITY
COMPACT DESIGN MOVES EASILY
AROUND THE JOB-SITE

ON-BOARD STORAGE
STORES ALL 881 BENDER
COMPONENTS



Bend Up To 4" Rigid Conduit
10' length, including off-set,
saddle and back-to-back bends
with ease & consistent accuracy



**COMBINES THE BRUTE FORCE
OF A 40 TON RAM WITH
MOBILITY, CONVENIENT
SET-UP AND STORAGE**



**Fits Through Standard
Height Doors 36" Wide**
Goes just about anywhere on
the construction site



Forks of the 881 Bender Unit
can fold down into the MBT for
convenient transport or storage



Pump basket swings out of the way
when not in use

**BENDING IS SET TO
WAIST HEIGHT
FOR COMFORT!**

Each component is pinned
into place for secure storage



**Carry ALL the components
you need when using your
881 Bender Unit!**



Ordering Information

Cat#	UPC#	Description	Qty
881-MBT	00903	Mobile Bending Table	1
881CT	31287	Cam Track Conduit Bender for One-Shot 90° Bends in 2-1/2", 3", 3-1/2" and 4" EMT, IMC and Rigid conduit, without hydraulic pump	1
881CTE980	34208	Cam Track Conduit Bender for One-Shot 90° Bends in 2-1/2", 3", 3-1/2" and 4" EMT, IMC and Rigid conduit, with 980 Electric Hydraulic Pump	1
881CTD	38466	Cam Track Conduit Bender for One-Shot 90° Bends in 2-1/2", 3", 3-1/2" and 4" EMT, IMC and Rigid conduit, without hydraulic pump & 3-1/2" shoe group	1
881CTDE980	38467	Cam Track Conduit Bender for One-Shot 90° Bends in 2-1/2", 3", 3-1/2" and 4" EMT, IMC and Rigid conduit, with 980 Electric Hydraulic Pump, without 3-1/2" shoe group	1
881BASIC	35711	Conduit Bender without shoe groups or hydraulic pump	1
27554	27554 ^A	2-1/2" – One Shot 90° EMT, IMC, Rigid Shoe Group	1
27555	27555 ^A	3" – One Shot 90° EMT, IMC, Rigid Shoe Group	1
31281	31281 ^A	3-1/2" – One Shot 90° EMT, IMC, Rigid Shoe Group	1
31274	31274 ^A	4" – One Shot 90° EMT, IMC, Rigid Shoe Group	1

^A = ACCESSORY

Specifications

Weight:	300 lbs. (136kg)
Weight Of Table With All Components:	1326 lbs. (601.5kg)
Length Of Table: <i>(not including conduit)</i>	67" (1.7m)
Overall Height:	With Pump: 41" (1.04m) Without Pump: 35" (0.89m)
Overall Width:	31 1/2" (0.8m)



www.greenlee.com MA-5760 12/18
4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2018 Greenlee Tools, Inc. • An ISO 9001 Company • Printed in USA