## 760237040 | CPP-UDDM-SL-1U-24

### Discrete Distribution Module Panel, SL, UTP, 1U, 24 port



#### Product Classification

PortfolioCommScope®Product TypeRJ45 patch panel

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

#### **Dimensions**

Depth, with cable management119.38 mm4.70 inDiameter Over Dielectric, maximum1.168 mm0.046 inDiameter Over Dielectric, minimum0.762 mm0.030 inHeight44.45 mm1.75 inWidth482.60 mm19.00 in

## **Electrical Specifications**

ANSI/TIA Category 5e | 6 | 6A

### **Environmental Specifications**

Flammability Rating UL 94 V-0

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Safety Standard CUL | RCM | UL

**Storage Temperature**  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

## General Specifications

Total Ports, quantity 24

Cable Type U/UTP (unshielded)

ColorBlackModules, quantity0Package Quantity1

Rack Type EIA 19 in Rack Units 1.0

## Mechanical Specifications

Panel Style Straight

page 1 of 2 January 21, 2019



# 760237040 | CPP-UDDM-SL-1U-24

**Material Type** 

High-impact, flame retardant, thermoplastic | Powder-coated steel

# Regulatory Compliance/Certifications

Classification **Agency** RoHS 2011/65/EU Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system





page 2 of 2 January 21, 2019