

## Mounting Bases, Cable Ties and Accessories

### Select the four-way configuration you need!

#### Four-Way Adhesive Mounting Base

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction
- For synthetic rubber adhesive (SRA), allow 15-minute setting time for maximum adhesion performance
- For acrylic adhesive, allow 24- to 72-hour setting time for maximum adhesion performance (acrylic-adhesive mounting bases may be re-positioned initially before the adhesive has set)



STD. PKG. CAT. NO.	BULK PKG. CAT. NO.	MOUNTING METHOD	MAX. TIE WIDTH ACCOM.	LENGTH IN./MM	WIDTH IN./MM	MATERIAL	STD. PKG. QTY.	BULK PKG. QTY.
<b>4-Way Adhesive Mounting Base</b>								
TC5345A	TC345A	SRA* Adhesive	.19	1.13/28.58	1.13/28.58	Nylon 6.6	100	1,000
—	TC345AFR	SRA* Adhesive	.19	1.13/28.58	1.13/28.58	Flame-Retardant Nylon	—	1,000
TC5345AX	TC345AX	SRA* Adhesive	.19	1.13/28.58	1.13/28.58	UV Black	100	1,000
TC5345AHTFR	—	Acrylic Adhesive	.19	1.13/28.58	1.13/28.58	Black High-Temp Flame-Retardant Nylon	100	1,000
—	TC345	TC2PA/Screws	.19	1.13/28.58	1.13/28.58	Nylon 6.6	—	1,000



STD. PKG. CAT. NO.	BULK PKG. CAT. NO.	MOUNTING METHOD	MAX. TIE WIDTH ACCOM.	LENGTH IN./MM	WIDTH IN./MM	MATERIAL	STD. PKG. QTY.	BULK PKG. QTY.
<b>4-Way Mini Base</b>								
TC050X050A-C	TC050X050A	SRA* Adhesive	.10	.5/12.70	.5/12.70	Nylon 6.6	100	1,000
TC5344A	TC344A	SRA* Adhesive	.14	.75/19.05	.75/19.05	Nylon 6.6	100	1,000
TC5344AX	TC344AX	SRA* Adhesive	.14	.75/19.05	.75/19.05	UV Black	100	1,000
TC5344	TC344	Screw Mount	.14	.75/19.05	.75/19.05	Nylon 6.6	100	1,000
<b>Large 4-Way Base</b>								
TC150X150A-L	TC150150A	SRA* Adhesive	.19	1.5/38.10	.50/38.10	Nylon 6.6	50	500
TC150X150AX-L	TC150X150AX	SRA* Adhesive	.19	1.5/38.10	.50/38.10	UV Black	50	500
—	TC200X200	Screw Mount	.30	2.0/50.80	2.0/50.80	Nylon 6.6	50	500
TC200X200A-L	TC200X200A	SRA* Adhesive	.30	2.0/50.80	2.0/50.80	Nylon 6.6	50	500
—	TC368	Screw Mount	.75	2.0/50.80	2.0/50.80	Nylon 6.6	—	500
—	TC368A	SRA* Adhesive	.75	2.0/50.80	2.0/50.80	Nylon 6.6	—	500



- Storage/Service Temperature: 32° F to 120° F (0° C to 48° C)
  - Application Temperature: 65° F to 100° F (18° C to 37° C)
  - Surface Preparation: Surface should be cleaned with alcohol-based (IPA) cleaner before application
- \*Synthetic Rubber Adhesive

**Note:** See product expiration date on packages with adhesive. Periodically check product for adhesion and replace as needed. Product is for wire management only and is not intended for use as a primary support of wire, cable, etc.

#### Two-and Four-Way Adhesive Mounting Base



- 4-way base for cable ties up to .184" maximum width and a two-way base for ties up to .301" maximum width
- May also be mounted with #8 size screw (2 holes)

STD. PKG. CAT. NO.	BULK PKG. CAT. NO.	MOUNTING METHOD	MAX. TIE WIDTH ACCOM.	LENGTH IN./MM	WIDTH IN./MM	MATERIAL	STD. PKG. QTY.	BULK PKG. QTY.
TC5347A	TC347A	SRA* Adhesive	.30	1.13/28.58	1.13/28.58	Nylon 6.6	100	1,000
TC5347AX	—	SRA* Adhesive	.30	1.13/28.58	1.13/28.58	UV Black	100	—
—	TC347	TC2PA/Screws	.30	1.13/28.58	1.13/28.58	Nylon 6.6	—	1,000
—	TC347FR	TC2PA/Screws	.30	1.13/28.58	1.13/28.58	Flame-Retardant	—	1,000
—	TC347X	TC2PA/Screws	.30	1.13/28.58	1.13/28.58	UV Black	—	1,000

Temperature Rating: 32° F to 120° F (0° C to 48° C) \*Synthetic Rubber Adhesive

**Note:** See product expiration date on packages with adhesive. Periodically check product for adhesion and replace as needed. Product is for wire management only and is not intended for use as a primary support of wire, cable, etc.