



Color: White

UPC Code: 078477683866

Country Of Origin: China

NEMA:
5-15R



T5632-W

Combination Duplex Receptacle/Outlet and USB Charger. 15 Amp, 125 Volt, Decora Tamper-Resistant Receptacle/Outlet, NEMA 5-15R. 3.6 Amps, 5VDC, 2.0 Type A USB Chargers. Grounding, Side Wired & Back Wired - White.

The Leviton USB Charger/Tamper-Resistant Duplex Receptacle offers two high-powered USB Ports with 3.6A of charging power and two 15A or 20A/125V Tamper-Resistant Receptacles. It has the capability to charge two USB powered electronic devices utilizing its two USB Ports, leaving the two Tamper-Resistant Receptacles free for other uses. The Leviton USB Charger/Tamper-Resistant Duplex Receptacle is designed to charge tablets, smart and mobile phones, gaming devices, e-readers, digital cameras and a host of other electronic devices.

Technical Information

Product Features

Amperage: 15 A
Brand: Decora
Grade: Residential/Commercial Specification Grade
Grounding: Grounding
Horsepower Rating: 15A-1/2 HP
NEMA: 5-15R
Ratings: 15A-125V
Type: Type A/A Duplex Receptacle
Voltage: 125 VAC

Electrical Specifications

Amperage: 15 A
Flammability: Rated V-0 per UL 94
Grounding: Grounding
Horsepower Rating: 15A-1/2 HP
Operating Temperature: -10°C to 40°C
Ratings: 15A-125V

Environmental Specifications

Body Material: Thermoplastic
Color: White
Cover Material: Thermoplastic
Flammability: Rated V-0 per UL 94
Operating Temperature: -10°C to 40°C
Strap Material: Steel

Material Specifications

Body Material: Thermoplastic
Color: White
Cover Material: Thermoplastic
Product ID: Stamped on Strap
Strap Material: Steel
Terminal Accom.: 14-12 AWG
Terminal ID: Brass-Hot Black-Hot White-Neutral Green-Gnd
Termination: Back & Side
Torque Range: 12-14 inch pounds

Mechanical Specifications

Amperage: 15 A
Color: White
Grade: Residential/Commercial Specification Grade
Product ID: Stamped on Strap
Terminal Accom.: 14-12 AWG
Terminal ID: Brass-Hot Black-Hot White-Neutral Green-Gnd
Termination: Back & Side
Torque Range: 12-14 inch pounds

Standards and Certifications

FCC Part 15: Class B
Listed: cCSAus
NOM: 057
Warranty: 5 Year Limited

Features and Benefits

- Perfect for use in residential applications such as kitchens, bedrooms and home offices and in commercial applications such as hotels, airports, restaurants and cafes, salons, office cubicles and college dorm rooms
- Smart chip recognizes and optimizes the charging requirements of individual devices
- USB Ports are positioned vertically providing more space for maneuvering and reducing stress on USB cables
- Compatible with USB 3.0, 2.0, 1.1 devices

- Fits in a standard wallbox, is compatible with standard wallplates and can be multi-ganged with other devices
- Easy to install. Can replace existing outlets

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

