




CAT. NO.	ACSR MAIN & TAP EQUAL	WIRE SIZE AWG OR kcmil CU or AL				A	B	C	D
		MAIN		TAP					
		MAX.	MIN.	MAX.	MIN.				
9HPS	_____	10	12	10	12	3/8	.146	1/2	29/32
8HPS	_____	8	12	8	12	3/8	.146	1/2	29/32
6HPS	8	6	12	6	12	15/32	.170	21/32	1-1/8
4HPS	6-8	4	12	4	12	17/32	.237	23/32	1-9/32
2HPS	4-8	2	8	2	8	19/32	.270	3/4	1-15/32
1HPS	2-8	1	8	1	8	11/16	.330	7/8	1-5/8
10HPS	1-6	1/0	6	1/0	6	3/4	.385	15/16	1-13/16
20HPS	1/0-6	2/0	6	2/0	6	7/8	.442	1-1/16	2-1/16
40HPS	4/0-4	4/0	4	4/0	4	1	.580	1-1/4	2-15/32
350HPS	266.8-1/0	350	250	350	1/0	1-1/4	.783	1-11/16	2-23/32
500HPS	397.5-1/0	500	400	500	2/0	1-1/2	.971	1-7/8	3-1/32
750HPS	666.6-4/0	750	600	750	4/0	1-15/16	1.291	2-1/4	3-21/32
1000HPS	900-477	1000	800	1000	4/0	2-1/4	1.416	2-17/32	4-1/32

SPECIFICATIONS

MATERIAL: SILICON BRONZE ALLOY

FINISH: TIN PLATE

CONNECTORS ARE UL CERTIFIED FOR COPPER CONDUCTOR ONLY

GENERAL NOTES		Color-Keyed® Thomas & Betts www.tnb.com			
1. DIMENSIONS IN PARENTHESES () ARE IN METRIC UNITS.					
REVISIONS		DESCRIPTION: BRONZE SPLIT BOLTS WITH SPACER			
—	SEE ERN (****) FOR APPROVAL SIGNATURES	ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:
	PROJECT NO: ****	C055361 / (2003886)	1 OF 1	—	WSD-000072