

LYRIQ HIGH PERFORMANCE KEYPAD POWER DISTRIBUTION MODULE

AU1001 | [On-Q](#)



FEATURES & BENEFITS

The lyriQ High Performance Power Module supports up to four lyriQ High Performance Keypads. It's a single-slot module and features dual power input connections.

- Automatically overrides the remote source
- For use with the lyriQ Audio System

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat 5e, Speaker Cable
 Color: Black
 Finish: Black Powder Coat
 Footprint: Single-Bay
 Performance Category: High Performance
 Termination: Terminal Block
 Product Series: Classic
 Type: High Performance Audio Distribution Module

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Mounting Plate and other hardware included

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 45111801

CONSTRUCTION INFORMATION

Installation Location: Enclosure

DIMENSIONS

Depth (Metric): 4.3 cm
 Depth (US): 1.7"
 Height (Metric): 7.4 cm
 Height (US): 2.9"

Width (Metric): 16.3 cm

Width (US): 6.42 in

TECHNICAL INFORMATION

Amps: 2.5A

Compatible Power Supplies: 24V, 2.5A PW1060 (not included)

Material: 18 Gauge Cold Rolled Steel

Mounting: Enclosure

Volts (DC): 24VDC