



## LYRIQ FLUSH MOUNT TRIPLE SOURCE INPUT

AU1011-WH | [On-Q](#)

### FEATURES & BENEFITS

This attractive input device is built directly into the wall and is used to quickly and easily connect input devices to be shared throughout the home, such as a home theater system, stereo receiver and an iPod.

- Automatically overrides the remote source
- For use with the lyriQ Audio System

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Product Series: Studio

#### CONSTRUCTION INFORMATION

Spec 1: Voltage Requirements

Installation Location: In-Wall

#### CORD INFORMATION

Pinning: RJ45 modular connector 1:

1. Green/White Audio L- (PreGND)
2. Green Audio L+ (S1)
3. Orange/White Audio R- (PreGND)
4. Blue IR\_IN (IR TX)
5. Blue/White Status\_Out (IR RX)
6. Orange Audio R+ (S1)
7. Brown/White Ground
8. Brown Power (+24Vdc)

RJ45 modular connector 2:

1. Green/White PreGND L- (S2)
2. Green Audio L+ (S2)

3. Orange/White PreGND R- (S2)
4. Blue Audio L+ (S3)
5. Blue/White PreGND L- (S3)
6. Orange Audio R+ (S2)
7. Brown/White PreGND R- (S3)
8. Brown Audio R+ (S3)

#### TECHNICAL INFORMATION

Frequency Response: 20 - 100Hz 4dB; 100 - 20,000Hz 2dB  
Humidity: Up to 90% RH (non-condensing)  
IR Receive Frequency: 10 KHz  $\pm$  5 KHz to 110 KHz  $\pm$  5 KHz  
Operating Temperature (Celsius): 0 to 55°C  
Output And Line Out Connection: Audio Out: RJ45 connector 1, & 2  
IR In: 3.5mm stereo audio jacks  
Power Requirements: +24Vdc supplied by the Distribution Module  
Storage Temperature: -25 to +75 Degrees Celsius