

---

## FOUR ROOM WHOLE HOUSE MUSIC & INTERCOM, OIL RUBBED BRONZE

ICAU16-OB | [On-Q](#)

---

### FEATURES & BENEFITS

Provides whole house audio and intercom.

**Kit Includes:**

- 1 **AU7396** Single Source 4 Zone Distribution Module
- 1 **AU1004-WH** Flush Mount Single Source Input
- 4 **AU7394-WH** IyriQ Classic Standard Performance Keypad Volume Control
- 4 **MS3650 3000 Series** 6.5inch In-Ceiling Speakers (pairs)
- 1 **IC1000** Broadcast Intercom Main Module
- 4 **IC1004-WH** Broadcast Intercom Room Stations
- 1 **F7601** Broadcast Intercom Door Chime Module
- 1 **IC1001** Audio Interrupt Module
- 1 **F7596-OB** Broadcast Intercom Door Station
- 1 **PW1060** 24v, 2.5 Amp Power Supply
- 1 **PW7725** 12v, 2.5Amp Power Supply
- 1 **WP1208-WH** Three Gang Decorator Wall Plate
- 1 **WP1205-WH** Single Gang Decorator Wall Plate
- 1 **F7425** Dual Head IR Emitter
- 1 **AU1060** IyriQ Dual Head IR Emitter

---

### SPECIFICATIONS

#### GENERAL INFO

Discontinued: Yes  
Cable Type: Cat 5, Speaker Cable  
Color: Oil Rubbed Bronze  
Type: Kit

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 45111801

#### CONSTRUCTION INFORMATION

Installation Location: Enclosure, Ceiling, Electrical Box

## TECHNICAL INFORMATION

Compatible Power Supplies: 1 24v 2.5 Amp Power Supply PW1060 (included), 1 12v 2.5Amp Power Supply PW7725 (included)

Power Peak: Speaker: 100W

Power RMS: Speaker: 50W

Speaker Depth (Metric): 8.36 cm

SpeakerDepth (US): 3.29 in

Speaker Impedance Load: 8 ohms

Tweeter Type: 1" PEI Mylar

Woofers Type: Mica Fiber