

---

## 48VDC, 60W POWER SUPPLY

PW1458 | [On-Q](#)



---

### FEATURES & BENEFITS

Powers the DA1458 8-Port Gigabit Switch by converting high voltage alternating current (AC) to direct current (DC). Specifically compatible with the Legrand DA1458: 8-Port Gigabit Switch with 4-Ports 802.3af PoE.



- Package includes a DC power supply with 2 ft. barrel connector plug and 1.5 ft. AC power plug
- IEC C13/C14 connections
- Stacks neatly in enclosure with AC1031 power strip

---

### SPECIFICATIONS

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
cULus: Yes  
FCC Standard: Yes

#### CONSTRUCTION INFORMATION

Material 1: High Impact Flame Retardant Plastic

#### DIMENSIONS

Depth (Metric): 35mm  
Depth (US): 1.38mm  
Height (Metric): 113mm  
Height (US): 4.4in  
Width (Metric): 49mm  
Width (US): 1.9in

#### TECHNICAL INFORMATION

AC Voltage Input: 100-240VAC

Amps: 1.25A

Operating Temperature (Celsius): 0°C to 40°C

Volts: 48VDC

Watts: 60W

Receptacle Type: DC Barrel Jack