



Standard Series DisplayPort Male To Male Cables

Ensure ultimate high definition performance from Comprehensive DisplayPort cables. DisplayPort is an exciting next generation display interface designed to transmit ultra high definition digital signals between computers, displays, flat panels, projectors and other high definition content applications. DisplayPort supports a up to 10.8 Gbit/s data rate and WQXGA (2560×1600) resolution. Comprehensive Standard Series DisplayPort cables feature premium cable construction with for sharp, high definition picture and sound. Dense braided shielding eliminates EM interference to ensure the best digital performance. Comprehensive DisplayPort cables feature a small latching connector, two-way display connectivity, 24 Bit color depth and up to 8 channel audio support. Comprehensive DisplayPort cables come with a Lifetime Warranty.



Features

- Ultra High Speed 10.8 Gbps speed
- Greater than 24 bit color depth
- 8 Channel digital audio support
- DPCP and HDCP Content Protection
- Premium Construction with dense braided shield to reduce EM interference
- RoHS Compliant
- Lifetime Warranty



Specifications

Performance Grade: Good

Connector Type 1: DisplayPort Latching Male

Connector Type 2: DisplayPort Latching Male

Bandwidth or Speed: Supports 10.8 Gbps

Gauge: 28AWG

Center Conductor: Tinned Copper

Connector Finish: Nickel

Shielding: 85% Braid

Refresh Rate: 120Hz

UL Rated: Yes

UL Rating: VW-1

Ferrite Cores: No

RoHS Compliant: Yes

Jacket Type: Xtra-Flex PVC

Temperature Rating: 80 deg C

Voltage: 30V

Warranty: Lifetime

DISP-DISP-3ST	3ft.
DISP-DISP-6ST	6ft.
DISP-DISP-10ST	10ft.
DISP-DISP-15ST	15ft.