



## Plenum Pro AV/IT 18G 4K High Speed Active HDMI 24 AWG with ProGrip®, SureLength® Cables

Comprehensive's Plenum Pro AV/IT 18G 4K Active HDMI Cables were designed specifically for commercial and residential system integrators as well as technology professionals in education, corporate, government, houses of worship and other demanding commercial environments. 25ft, 35ft and 50ft lengths utilize advanced active chip technology to deliver a full 4K 18G signal with 4:4:4 Color Space signal. Cables are active and directional.

Plenum Pro AV/IT 18G 4K Active High-Speed HDMI cables come equipped with all the latest HDMI features including Ultra HD 4K@60Hz 4:4:4 chroma sampling and 18Gbps bandwidth rating (end to end), transmission of High Dynamic Range (HDR) video, Ethernet, Deep Color, up to 32 audio channels with ARC, support for wide angle theatrical 21:9 aspect ratio.



**DOLBY.** **Sure Length** **HDCP** **HDR** **ULTRA HD** **Pro Grip** **4:4:4 COLOR SPACE** **HDMI** **4K60 18GB**



### Features

- 24 gauge Heavy Duty construction
- 18Gbps High Speed (End to End)
- CL2P rated for installations in plenum spaces
- Deep Color and x.v. Color
- 120 Hz Refresh Rate
- 5.1/7.1 Lossless Dolby TrueHD and DTS-HD Surround Sound
- Audio Return Channel
- 3-D and Ethernet Capable
- 4K resolution support
- Lip-sync
- HDCP Compliant
- Premium Molded 24k Gold Plated HDMI male connectors on each end
- ProGrip® low profile connector utilizes up to 16 lbs of retention force to help keep connector in place
- SureLength® cable length indicators make it easy to organize for installations
- Triple Shielded
- 4K UHD resolution
- RoHS Certified
- Lifetime Warranty

### Specifications

Performance Grade: Best  
Connector Type 1: HDMI Male with ProGrip  
Connector Type 2: HDMI Male with ProGrip  
Bandwidth or Speed: up to 18Gbps  
Resolution: Up to 4K UHD  
Gauge: 24AWG Please note: Lengths 25ft, 35ft, 50ft are active and directional  
Center Conductor: Bare Copper  
Connector Finish: 24K Gold Plated  
Shielding: Triple Shielded, Inner 100% Aluminum Mylar Wrap, Outer 100% Aluminum Mylar Wrap, 85% Tinned Copper Braid  
HDCP and CEC Compliant: Yes  
Category 2 Certified: Yes  
Ethernet Capability: Yes

Supports Audio Return Channel: Yes  
3D Ready: Yes  
Longer Distance Capability: Yes  
Heavy Duty Construction: Yes  
UL Rated: Yes  
UL Rating: CL2P  
RoHS Compliant: Yes  
Cable Outer Diameter: 0.41" (10.5 mm)  
Jacket Type: Plenum  
Jacket Color: Black  
Temperature Rating: 75°C  
Voltage: 30V  
Warranty: Lifetime

<b>HD18G-25PROPA</b>	25ft
<b>HD18G-35PROPA</b>	35ft
<b>HD18G-50PROPA</b>	50ft



## Plenum Pro AV/IT 18G 4K High Speed Active HDMI 24 AWG with ProGrip<sup>®</sup>, SureLength<sup>®</sup> Cables

HDMI CABLES

