

## MicroFlex Low Profile DVI-D Cables

These are easily the most flexible DVI cables on the market today. Their low profile design and un-heard of flexibility make them perfect for use in surface access boxes, equipment racks and other tight spaces. The pro grade construction consists of a smaller 30 awg tinned copper contruction for superior digital image quality and speeds up to 10.2 Gbps. Premium shielding ensures proper rejection of EM and RF interference. This versatile cable supports resolutions of up to 1900x 1200 @ 60 Hz and 1080p. Gold plated contacts and our famous Lifetime Warranty come standard.



## **Features**

- · Perfect for surface access boxes and other tight spaces
- State of the Art Flexibility
- Supports DVI-D Single Link up to 1900x 1200 @ 60 Hz and 1080p
- High Speed up to 10.2Gbps
- 30 Awg Copper Construction
- · Low Bend Radius
- Gold Plated Contacts
- Lifetime Warranty



## **Specifications**

Performance Grade: Better Connector Type 1: DVI-D Male Connector Type 2: DVI-D Male Bandwidth or Speed: Up to 10.2 Gbps

Resolution: Up to 1080p Construction: Single Link

Gauge: 30AWG

Center Conductor: Tinned Copper Connector Finish: 24K Gold Plated

Shielding: Triple Shielded, Inner 100% Aluminum Mylar Wrap, Outer 100% Aluminum Mylar Wrap, 85% Tinned Copper Braid

UL Rated: Yes UL Rating: VW-1 RoHS Compliant: Yes Jacket Type: Xtra-Flex PVC Jacket Color: Black

Temperature Rating: 80 deg C

Voltage: 30V Warranty: Lifetime





MDVI-MDVI-18INPRO	1.5ft
MDVI-MDVI-3PRO	3ft
MDVI-MDVI-6PRO	6ft
MDVI-MDVI-10PRO	10ft
MDVI-MDVI-15PRO	15ft