

# CS-16C II

## 6.5" In-Ceiling Speaker



### GOOD SOUND FOR ANY ROOM

Using the same design principles of our premium architectural and box speaker lines, the all new Klipsch Contractor series delivers true Klipsch power and performance to any budget. With a 6.5" Polymer woofer and a 1" Polymer Dome tweeter the CS-16C II brings dynamic, powerful, detailed Klipsch sound to your distributed audio, home theater, or 2-channel system.

### PATENT-PENDING SKYHOOK™ TOOL-FREE INSTALLATION SYSTEM

The exclusive installation system engages the dog legs automatically when the speaker is inserted into the cutout hole with a preset clamping force, eliminating the possibility of overtorquing. This fast, easy installation system reduces install time by up to 75%.

### ALL NEW, BEZEL-FREE MAGNETIC GRILLE

A completely redesigned powdercoated magnetic steel grille eliminates the bezel for seamless, pristine integration into the living space.

### SPECIFICATIONS

<b>FREQUENCY RANGE</b>	65Hz - 20kHz +/- 3dB
<b>HIGH FREQUENCY DRIVER</b>	1" (2.54cm) Polymer Dome Tweeter
<b>LOW FREQUENCY DRIVER</b>	6.5" (16.51cm) Polymer Woofer
<b>SENSITIVITY</b>	91 dB @ 2.83V / 1m
<b>POWER HANDLING</b>	40W RMS / 160W Peak
<b>IMPEDANCE</b>	8 Ohm Compatible
<b>ENCLOSURE MATERIAL/TYPE</b>	ABS/Infinite Baffle
<b>FINISH</b>	Black Baffle/Frame, White Paintable Grille
<b>PRODUCT DIMENSIONS</b>	9.2" W x 9.2" H x 4.5" D (23.3cm H x 23.3cm W x 11.3cm D)
<b>MOUNTING DEPTH</b>	4.34" (11.03cm)
<b>CUTOUT DIMENSIONS</b>	8.3" (21.1cm)
<b>PRODUCT WEIGHT</b>	7 lbs (3.18kg)
<b>INCLUDED IN BOX</b>	Flat Paintable Magnetic Grille
<b>INSTALL KIT</b>	IK-650-C II (Sold Separately)
<b>FIRE RATED ENCLOSURE</b>	ME-650-C (Sold Separately)
<b>BUILT FROM</b>	2017