

Optolinx IMC-100A

Industrial 10/100BaseTX to 100BaseFX Industrial Media Converter




Features

- ▶ UTP to Fiber Media Converter
- ▶ RJ-45 Port Support Auto MDI/MDI-X Function
- ▶ Auto Negotiation Speed, Half/Full Duplex
- ▶ Store-and-Forward Switching Architecture
- ▶ Built-in Link Loss Forwarding (LLF) & Link-Fault-Pass-Through (LFP)
- ▶ Wide-range Redundant Power Design
- ▶ Power Polarity Reverse Protection
- ▶ Overload Current Protection
- ▶ DIN-Rail or Wall Mountable
- ▶ UL Class I, Division 2 Certified
- ▶ IP30 Protection
- ▶ 5-Year Warranty



Specifications



► Specifications

Standard

IEEE 802.3 10BaseT Ethernet
IEEE 802.3u 100BaseTX/100BaseFX
IEEE 802.3x Flow Control and Back-Pressure

Connector

Fiber: SC/ST (Multi-Mode), SC/ST (Single-Mode, 30Km)
RJ-45 Socket: CAT-3/5 (10/100Mbps) Twisted Pair Cable
Auto MDI/MDI-X & Auto-Negotiation Function Support

Switch Architecture

Store and Forward

Fiber Parameters

Fiber Core: Multi-Mode (62.5/125um ~ 50/125um)
Single-Mode (9/125um ~ 10/125um)
Wavelength: 1310nm
Fiber Distance: Multi-Mode Fiber 2Km
Single-Mode Fiber 30Km

Link Loss Forward

TX → Fiber: If TX port link down, will force Fiber port to link down
Fiber → TX: If Fiber port link down, will force TX port to link down

DIP Switch

DIP 1: ON = Enables Port/Power Alarm
OFF = Disables Port/Power Alarm
DIP 2: ON = Enables Link Loss Forward & Link-Fault-Pass-Through
OFF = Disables Link Loss Forward & Link-Fault-Pass-Through
DIP 3: ON = 100BaseFX Half-Mode
OFF = 100BaseFX Full-Mode
DIP 4: ON = 100BaseTX Full-Duplex Mode
OFF = Auto-Negotiation

LED

Unit: Power, Power 1, Power 2 (Green), Fault (Red)
TX: Link/Act (Green), 100M (Yellow)
Fiber: Link/Act (Green), Full Duplex/Collision (Yellow)

Power

DC 12 ~ 48V
Redundant power with reverse polarity protection and removable terminal block

Power Consumption

2.74 Watts

Reserve Polarity/Overload Current Protection

Present

Mechanical

Casing: IP30 Metal Case
Dimension (W x H x D): 30 x 140 x 95 mm (1.18 x 5.51 x 3.74 in.)
Installation: DIN-Rail/Wall Mountable

Operation Temperature

Standard: -10° C to 70° C (14° F to 158° F)
Wide Operating Temperature: -40° C to 80° C (-40° F to 176° F)

Operation Humidity

5% to 95% (Non-condensing)

Storage Temperature

-40° C to 85° C

EMI

FCC Class A
CE EN6100-4-2/EN6100-4-3/EN6100-4-4/EN6100-4-5/EN6100-4-6/
EN6100-4-8/EN6100-4-11/EN6100-4-12/EN6100-6-2/EN6100-6-4

Safety

UL/cUL Class I, Division 2
CE EN60950-1

Stability Testing

Shock: IEC60068-2-27
Free Fall: IEC60068-2-32
Vibration: IEC60068-2-6

Warranty

5-Year Warranty

► Ordering Information

IMC-100A-M

IMC-100A-S3

IMC-100A-M-T

IMC-100A-S3-T

IMC-100A-ST-M

IMC-100A-ST-S3

IMC-100A-ST-M-T

IMC-100A-ST-S3-T

Industrial Media Converter, Multi-Mode Fiber, SC, 2 Km

Industrial Media Converter, Single-Mode Fiber, SC, 30 Km

Industrial Media Converter, Multi-Mode Fiber, SC, 2 Km, Wide Operating Temperature

Industrial Media Converter, Single-Mode Fiber, SC, 30 Km, Wide Operating Temperature

Industrial Media Converter, Multi-Mode Fiber, ST, 2 Km

Industrial Media Converter, Single-Mode Fiber, ST, 30 Km

Industrial Media Converter, Multi-Mode Fiber, ST, 2 Km, Wide Operating Temperature

Industrial Media Converter, Single-Mode Fiber, ST, 30 Km, Wide Operating Temperature

Optional Accessories

DR-4524

DR-75-24

DR-120-24

45W 24VDC Industrial DIN Rail Power Supply

75W 24VDC Industrial DIN Rail Power Supply

120W 24VDC Industrial DIN Rail Power Supply