



BURNDY Catalog Number
UPC Number
Description
Status

YAD28M10E38
 7818105495444
 4/0 STR FLEX 3/8 STUD
 Active

Web Use
 BURNDY Product Line

Dimensional	
Pin Diameter	1.73
Length (in)	2.20
Outside Diameter	0.89
Thickness	0.12
B Length (in)	0.87
Pad Width (in)	0.95
Hole Size (in)	0.41
Strip Length	1
General	
Product Description	Non-Insulated Brazed Barrel Copper Terminal, 3/8", 2.20 in L, Tin Plated, Ring Tongue
Conductor(s)	
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG
Physical	
Type of Plating	Tin
Plated (Yes or No)	Y
Approvals / Certifications	
UL Listed	N
CSA Certified	N
ROHS Compatible	Non-Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175