



BURNDY Catalog Number
UPC Number
Description
Status

YAD1CM10E38
7818105492166
1 STR CU FLEX 3/8 STUD
Active

Web Use
BURNDY Product Line

Dimensional

Pin Diameter	1.34
Length (in)	1.69
Outside Diameter	0.57
Thickness	0.07
B Length (in)	0.63
Pad Width (in)	0.71
Hole Size (in)	0.41
Strip Length	3/4

General

Product Description	Non-Insulated Brazed Barrel Copper Terminals, 3 / 8 " , 1 . 6 9 in L , Tin Plated, Ring Tongue
---------------------	--

Conductor(s)

Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	1 AWG

Physical

Type of Plating	Tin
Plated (Yes or No)	Y

Approvals / Certifications

UL Listed	N
CSA Certified	N
ROHS Compatible	Non-Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175