



MOTOR CONNECTION KITS (MCK)

HEAT SHRINK MOTOR CONNECTION KITS FOR 1/C (2000 V)

KEY FEATURES

- For use as an in-line or stub splice between 1/C poly feeder cable and motor leads.
- Excellent insulation sealing and resistance to abrasion in motor connections
- Qualified to ANSI-C119.1 and rated to ICEA electrical withstand test for 1000V

TE Connectivity's (TE) Raychem MCK connection kits come in two main types, Type V and Type L.

The stub "Type V" kit is designed to splice the stub or butt configuration that is commonly used where there is insufficient room to make in-line connections.

The In-Line "Type L" kit is used where space permits to splice, in-line connections.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



PRODUCT SELECTION INFORMATION: DIMENSIONS IN INCHES (mm)

Description	Motor Feeder Size (AWG/kcmil)	Bolt Length (max.)	Connection Length (max.) H	Length (Nominal)	Standard Pack
Stub Type V				Cap	
MCK-1V	#14 - #10	0.625	2.0 (51)	2.5 (64)	5
MCK-2V	#12 - #4	0.75	2.5 (64)	3.4 (86)	5
MCK-3V	#2 - 4/0	1	3.5 (89)	4.5 (114)	5
MCK-4V	250 - 500	1.5	4.5 (114)	6.5 (165)	5
In-Line Type L				Sleeve	
MCK-1L	#8 - 4/0	1.25	5.0 (127)x	9.0 (229)	5
MCK-2L	250 - 1000	1.25	8.0 (203)	12.0 (305)	5

* Dimension values provided are typical.
Related test reports: EDR-5110
Designed for single hole connectors.

ORDERING INFORMATION

Kit includes caps and sealent strips for three connections but do not contain connectors. Bulk options are also available. Consult your TE representative.

te.com/energy

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved. E568 10/2014

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Benelux:	+ 32 16 351 731
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
China:	+ 86 (0) 400-820-6015