



IN-LINE SPLICE (HVS 1/C) FOR 1/C SHIELDED CABLE (5 - 35 kV)

KEY FEATURES

- Kits contain a solderless grounding kit, consisting of a ground clamp, a ground braid, and shielding mesh
- Heat-shrink feature allows the kits to accommodate out-of-round, out-of-spec cable.

TE Connectivity's (TE) Raychem heat-shrinkable shielded power cable splices are pre-engineered to offer a compact, low-profile installation with a minimum diameter buildup.

Qualified to IEEE 404. For use on copper tape, wire shield, lead sheath, and UniShield cables. Some kits contain tube for outer layer.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



PRODUCT SELECTION INFORMATION: DIMENSIONS IN INCHES (mm)

Description	Conductor Size (AWG/kcmil)		Insulation Diameter (min. - max.)	Jacket O.D. (max.)	Maximum Connector Dimensions		Kit Installed Length	Required Installation Space
	5 kV	5/8 kV			OD	Length		
HVS 820S Series								
HVS-821S	#6 - 2/0	#6 - #2	0.35 - 0.65 (9 - 17)	0.80 (20)	0.50 (13)	3 (76)	24 (610)	44 (1118)
HVS-822S	3/0 - 300	#1 - 4/0	0.55 - 0.90 (14 - 23)	1.15 (29)	0.75 (19)	4.25 (108)	24 (610)	45 (1143)
HVS-823S	350 - 750	250 - 350	0.55 - 0.90 (14 - 23)	1.80 (46)	1.10 (28)	6 (152)	27 (686)	50 (1270)
HVS-824S	1000 - 1500	500 - 750	1.00 - 1.60 (25 - 41)	2.30 (58)	1.45 (37)	8 (203)	30 (762)	56 (1422)
HVS-825S	-	750 - 1000	1.30 - 2.25 (33 - 57)	2.45 (62)	1.85 (47)	8 (203)	30 (762)	56 (1422)
HVS 1520S Series		15 kV						
HVS-1521S	-	2/4/00	0.65 - 1.05 (17 - 27)	1.25 (32)	0.90 (23)	4.25 (108)	27 (686)	54 (1372)
HVS-1522S	-	250 - 350	0.90 - 1.30 (23 - 33)	1.50 (38)	1.20 (30)	5.5 (140)	28 (711)	56 (1422)
HVS-1523S	-	500 - 750	1.10 - 1.60 (28 - 41)	1.85 (47)	1.60 (41)	8 (203)	30 (762)	59 (1499)
HVS-1524S	-	750 - 1000	1.25 - 1.80 (32 - 46)	2.10 (53)	1.85 (47)	8 (203)	34 (864)	67 (1702)
HVS-1525S	-	1250 - 2000	1.60 - 2.50 (41 - 64)	2.80 (71)	2.40 (61)	8 (203)	40 (1016)	74 (1880)
HVS 1520S-W (15 kV) with Wraparound Rejacketing Sleeve		15 kV						
HVS-1521S-W	-	#2 - 4/0	0.65 - 1.05 (17 - 27)	1.25 (32)	0.90 (23)	4.25 (108)	28 (711)	39 (990)
HVS-1522S-W	-	250 - 350	0.90 - 1.30 (23 - 33)	1.50 (38)	1.20 (30)	5.5 (140)	28 (711)	40 (1016)
HVS-1523S-W	-	500 - 750	1.10 - 1.60 (28 - 41)	1.85 (47)	1.60 (41)	8 (203)	30 (762)	45 (1143)
HVS-1524S-W	-	750 - 1000	1.25 - 1.80 (32 - 46)	2.10 (53)	1.85 (47)	8 (203)	34 (864)	49 (1244)
HVS-1525S-W	-	1250 - 2000	1.60 - 2.50 (41 - 64)	2.80 (71)	2.40 (61)	11 (279)	40 (1016)	54 (1371)
HVS 2520 S (25 kV)		15 kV						
HVS-2521S	-	#1 - 250	0.90 - 1.20 (23 - 31)	1.50 (38)	1.10 (28)	4.00 (102)	40 (1016)	56 (1422)
HVS-2522S	-	350 - 500	1.20 - 1.50 (31 - 38)	1.95 (50)	1.35 (34)	6.0 (152)	40 (1016)	60 (1524)
HVS-2523S	-	750 - 1000	1.50 - 1.80 (38 - 46)	2.40 (61)	1.85 (47)	8 (203)	40 (1016)	62 (1575)
HVS-T-1580 (15 kV)								
HVS-3521S	-	1/0 - 3/0	0.95 - 1.35 (24 - 34)	1.55 (39)	1.20 (30)	4.00 (102)	40 (1016)	53 (1346)
HVS-3522S	-	4/0 - 600	1.20 - 1.70 (31 - 43)	2.10 (53)	1.50 (38)	6.0 (152)	44 (1118)	40 (1016)
HVS-3523S	-	600 - 1000	1.55 - 2.15 (39 - 55)	2.80 (71)	1.85 (47)	10 (254)	44 (1118)	45 (1143)

*All selections are based on the typical dimensions of 100% insulated cables, manufactured in accordance with AEIC standard Nominal insulation thickness (100%): 5 kV: 90 mils , 5/8 kV: 115 mils , 15 kV: 175 mils , 25 kV: 260 mils , 35 kV: 345 mils.
 If you have any questions, contact your TE Connectivity sales engineer or representative.
 For cables manufactured to other specifications, confirm selection with cable and connector dimensions.
 HVS-SHIM kits are available if the diameter of one of your cables is not within the standard range.
 Kits do not contain connectors; order compression or solder connectors separately.
 If external grounding is required, order an HVS-EG kit Standard package: 1 kit/box

TEST REPORT

HVS 5-8 kV: EDR-5181
 HVS 15 kV: EDR-5114
 HVS 25 kV: EDR-5150
 HVS 25-35 kV: EDR-5197
 HVS-1520S-W: EDR-5225e

te.com/energy

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved. E574 10/2014

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA: +1 800 327 6996
 France: +33 380 583 200
 UK: +44 0870 870 7500
 Germany: +49 896 089 903
 Spain: +34 916 630 400
 Benelux: +32 16 351 731
 Canada: +1 (905) 475-6222
 Mexico: +52 (0) 55-1106-0800
 Latin/S. America: +54 (0) 11-4733-2200
 China: +86 (0) 400-820-6015