

SD365CO

Multi-Criteria Fire/CO Detector



General Description

SD365CO is a plug-in, addressable device that provides both fire and carbon monoxide (CO) detection. The detector combines four separate sensing elements in one unit to sense multiple components of a fire: smoke, CO, light/flame, and heat. This approach enables enhanced sensitivity to real fire with heightened immunity to nuisance particulates. For CO, the detector's electrochemical sensing cell creates a separate signal for life safety CO detection.

Multiple sensors and communication can greatly reduce nuisance alarms compared to single sensing methods. Sophisticated algorithms maximize the advantages of the sensor types creating our best detection strategy offering heightened immunity to nuisance particulate and enhanced sensitivity to real fire.

- Photoelectric sensors detect airborne particles associated with smoke.
- Thermal sensors detect heat and rate-of-rise (135°F fixed temperature threshold).
- Carbon Monoxide sensors detect this by-product of fire for accurate fire detection.
- Infrared sensors discern light patterns in the environment as an additional data point for alarm determination.

This ability to reject certain nuisance alarm triggers, such as theater smoke, supports the use of the fire/CO detector in applications where moderate to heavy nuisance conditions exist that might cause single sensing detectors to false alarm.

The fire/CO detector meets both UL 268 and UL 521 listing requirements for fire detection as well as the UL 2075 standard for system-connected life safety carbon monoxide detection.

Released through the incomplete burning of various fuels, CO is a colorless, odorless and deadly gas that is virtually impossible to detect with the human senses. Because the potential exists for dangerous levels of CO to accumulate in almost any building, legislation mandating the use of CO detection in commercial spaces continues to grow.

B200S series intelligent sounder bases are recommended for use with SD365CO. These bases can generate either a Temp 3 pattern for fire or a Temp 4 pattern for CO alarm indication. The B200S series bases recognize the System Sensor synchronization protocol, for use as a component of the general evacuation signal — along with other System Sensor horns, horn strobes, and chimes — when connected to a power supply or Fire Alarm Control Panel (FACP) output capable of generating the System Sensor synchronization pulses.

Features

- Unique ability to detect all four major elements of a fire
- Separate CO detection signal
- Highest nuisance alarm immunity
- Automatic drift compensation for smoke and CO sensors
- Uses only one address on the SLC
- RealTest® CO testing capability
- UL 268, UL 521, and UL 2075 listed
- Separate audible signal for fire or CO alarm when used with a B200S series base
- 10-year CO cell with end-of-life warning
- New modern profile
- Expanded color options



SD365CO Multi-Criteria Fire/CO Detector
installed in B200S-LF-WH sounder base

Specifications

PHYSICAL

- Height: 2.7" (69 mm) installed in B200S series sounder base
- Diameter: 6.875" (175 mm) installed in B200S series sounder base
- Weight: 3.4 oz. (95 g)
- Color: White
- Operating Humidity Range: 15% to 90% Relative Humidity, Non-condensing
- Operating Temperature Range: 32°F to 100°F (0°C to 38°C)
- Air Velocity: 0 to 4000 ft./min. (0 to 1219.2 m/min.)

ELECTRICAL SPECIFICATIONS

- Operating Voltage Range: 15 to 32 VDC
- Operating Current @ 24 VDC: 200 uA (one communication every 5 seconds with green LED blink on communication)
- Maximum Alarm Current: 2 mA @ 24 VDC (one communication every 5 seconds with red LED solid on)
- Maximum Current: 4.5 mA @ 24 VDC (one communication every 5 seconds with amber LED solid on)
- Isolator Load Rating: 0.0063

CO MONITORING UL STANDARD REFERENCE

Alarm thresholds are as follows:

Parts Per Million	Detector Response Time
70 ± 5ppm	60 – 240 min.
150 ± 5ppm	10 – 50 min.
400 ± 10ppm	4 – 15 min.

Standards

Per UL standard 2075, the SD365CO has been tested to the sensitivity limits defined in UL Standard 2034.

UL Standard: UL 268

Agency Listings and Approvals

The listings and approvals below apply to the SD365CO. In some cases, certain modules may not be listed by certain approval agencies, or listing may be in process. Consult the factory for the latest listing status.

UL: S1059

CSFM: 7272-0075:0507

Ordering Information

SD365CO: Advanced multi-criteria fire/CO detector, LiteSpeed®, white

BASES

B501-WHITE: 4" Mounting base, white

B501-WHITE-BP: 4" mounting base, white, 10-pack

B501-IV: 4" Mounting base, ivory

B501-BL: 4" Mounting base, black

B300-6: 6" Flanged mounting base, white

B300-6-BP: 6" Flanged mounting base, white, 10-pack

B300-6-IV: 6" Flanged mounting base, ivory

B200S-WH: Intelligent addressable sounder base, white

B200S-IV: Intelligent addressable sounder base, ivory

B200S-LF-WH: Intelligent addressable sounder base, low-frequency, white

B200S-LF-IV: Intelligent addressable sounder base, low-frequency, ivory

B224BI-WH: Isolator base, white

B224BI-IV: Isolator base, ivory

B224RB-WH: Relay base, white

B224RB-IV: Relay base, ivory

ACCESSORIES

SMB600: Surface mounting kit (flanged)

TR300: Trim ring, white

TR300-IV: Trim ring, ivory

CK300-IR: IR color kit (includes cover and trim ring), white, 10-pack

CK300-IR-IV: IR color kit (includes cover and trim ring), ivory, 10-pack

CK300-IR-BL: IR color kit (includes cover and trim ring), black, 10-pack.

RA100Z: Remote LED annunciator

M02-04-00: Detector test magnet

M02-09-00: Telescoping test magnet

Fire•Lite® Alarms®, LiteSpeed®, and RealTest® are registered trademarks of Honeywell International Inc.

©2019 by Honeywell International Inc. All rights reserved. Unauthorized use of this document is strictly prohibited.



This document is not intended to be used for installation purposes.
We try to keep our product information up-to-date and accurate.
We cannot cover all specific applications or anticipate all requirements.
All specifications are subject to change without notice.

For more information, contact Fire•Lite Alarms Phone: (800) 627-3473, FAX: (877) 699-4105.
www.firelite.com

Country of Origin: Mexico