


# H-MSM Conduit/Pipe to Flange Clip, Side Mount – 812M24SM



- Supports conduit/pipe or cable from beam flanges
- Snap close clip pivots a full 360°
- Requires only a hammer to install



Part Number	812M24SM
Material	Spring Steel
Finish	nVent CADDY Armour
EMT Conduit Size	1/2" 3/4"
Rigid Conduit/Pipe Size	1/2" 3/4"
Outer Diameter (OD)	0.709" – 1.181"
Flange Thickness (FT)	1/8" – 1/4"
Static Load (F)	25 lb
Certifications	cULus
Standard Packaging Quantity	100 pc
UPC	78285611210
EAN-13	8711893600544

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

