


nVent CADDY Cat HP J-Hook with Hammer-On Flange Clip – CAT32HP912SM



- Requires only a hammer to install
- Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic
- Provides superior fill capacity and load rating over most other non-continuous cable support alternatives
- Rounded edges on J-Hooks provide proper bend radius support for high performance data cables
- Cost effective alternative to expensive cable tray
- Complies with EN 50174-2
- Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



| | |
|------------------------|--|
| Part Number | CAT32HP912SM |
| Material | Steel Spring Steel |
| Finish | Pregalvanized nVent CADDY Armour |
| Diameter (Ø) | 2" |
| Area | 3.97 in ² |
| Cable Capacity, Cat 5e | 90 |
| Cable Capacity, Cat 6 | 60 |
| Cable Capacity, Cat 6A | 35 |
| Flange Thickness (FT) | 1/2" – 3/4" |
| Static Load (F) | 60 lb |
| Certifications | cULus DIN 4102-12 abP P-3117/339/14-MPA BS (Germany) E30 E60 E90 |

| | |
|-----------------------------|---------------|
| Part Number | CAT32HP912SM |
| Standard Packaging Quantity | 50 pc |
| UPC | 78285680132 |
| EAN-13 | 8711893134728 |

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.
Cable capacity is calculated based on a 70% fill rate.

ANSI is a registered trademark of American National Standards Institute. ISO is a registered trademark of International Organization for Standardization. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

