nVent CADDY Cat HP J-Hook with Z Purlin Clip, Swivel - CAT48HP123







- Requires only a hammer to install
- Rotates 360 degrees to support various directional runs of cable
- Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic
- Provides superior fill capacity and load rating over most other non-continuous cable support alternatives
- Rounded edges on J-Hooks provide proper bend radius support for high performance data cables
- Cost effective alternative to expensive cable tray
- Complies with EN 50174-2
- Meets ISO[®]/IEC 14763-2, ANSI[®]/TIA 568 and ANSI[®]/TIA 569





D AN I	047/04/0400
Part Number	CAT48HP123
Material	Steel Spring Steel
Finish	Pregalvanized nVent CADDY Armour
Diameter (Ø)	3"
Area	9.26 in ²
Cable Capacity, Cat 5e	200
Cable Capacity, Cat 6	150
Cable Capacity, Cat 6A	80
Flange Thickness (FT)	0.06" - 0.10"
Static Load (F)	60 lb
Certifications	cULus
Standard Packaging Quantity	25 pc
UPC	78285684768
EAN-13	8711893143270

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2. Cable capacity is calculated based on a 70% fill rate.



ANSI is a registered trademark of American National Standards Institute. ISO is a registered trademark of International Organization for Standardization. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

nevent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent 's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

