

AXIS Camera Station S2212 Appliance

All-in-one recorder with integrated 12 channel PoE switch for high-definition surveillance

AXIS Camera Station S2212 Appliance is an all-in-one recording solution with integrated, manageable PoE switch designed to deliver reliable high-definition surveillance with up to 4K resolution. For quick and easy installation, AXIS S2212 is preconfigured and preloaded with AXIS Camera Station video management software, and includes licenses for 12 channels plus all necessary system software. AXIS Camera Station offers an intuitive user interface that allows users to take full advantage of Axis wide range of video surveillance cameras and other IP products. With the operating system stored on a solid-state drive (SSD) and 3-year hardware warranty, AXIS S2212 provides a reliable surveillance solution.

- > [All-in-one solution with integrated PoE switch](#)
- > [High-definition surveillance with up to 4K resolution](#)
- > [AXIS Camera Station licenses included](#)
- > [Full compatibility with Axis products](#)



AXIS Camera Station S2212 Appliance

Licenses	Includes 12 AXIS Camera Station Core Device licenses	12x PoE ports 10/100 Mbps
Processor	Intel® Core i3	1x SFP 10/100/1000 Mbps
Memory	8 GB RAM	1x RJ45 10/100/1000 Mbps
Storage	6 TB (1x6 TB) Surveillance Class HDD Additional storage: 1 free bay	Rear side Server: 1x RJ45 10/100/1000 Mbps
Switch	12 ports integrated, 135 W total power budget Power over Ethernet (PoE) IEEE 802.3at Class 4	2x USB 2.0 1 Displayport™ 1 HDMI port
Graphic card	Intel® HD Graphics 630	Operating conditions
Operating system	Microsoft® Windows® 10 IoT Enterprise Operating system recovery: yes Operating system drive: 120 GB SSD	0 °C to 40 °C (32 °F to 104 °F) Humidity: 10–90% RH (non-condensing)
Video streaming	Live view: 1 x 4K stream full screen 4 split x 1080p Up to 12 cameras split view Supports two monitors, maximum one 4K monitor recommended Playback: Supports the same split scenarios as live view Supports only one monitor	Storage conditions
Recording	Qualified for recording with a total recording rate up to 192 Mbit per second	-40 °C to 65 °C (-40 °F to 149 °F)
Power	Max 270 W, 135 W PoE dedicated 100 - 240 V AC, 3.5 A, 50/60 Hz 54 V DC, 5 A External power adapter	Approvals
Connectors	Front side: 1x USB 3.0 1x Audio line in 1x Audio line out Rear side Switch:	EMC CNS 13438, EAC, EN 55024, , EN 61000-3-2, EN 61000-3-3, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-003 Class A, KC KN32 Class A, KC KN35, RCM AS/NZS CISPR 32 Class A, VCCI Class A Safety IEC/EN 60950-1, IEC/EN 62368-1, KC-Mark, UL 62368-1
		Dimensions
		330 x 230 x 78 mm (13 x 9.1 x 3.1 in)
		Weight
		5.8 kg (12.8 lb)
		Included accessories
		Rack ears, power adapter
		Optional accessories
		Surveillance Hard Drive Axis desktop terminals Axis Ethernet surge protector For more accessories, see axis.com
		Warranty
		Axis 3-year warranty and AXIS Extended Warranty option, see axis.com/warranty

AXIS Camera Station

For details about AXIS Camera Station features and functions, see the AXIS Camera Station datasheet on axis.com

Environmental responsibility:

www.axis.com/environmental-responsibility