


VITALink®

16 AWG Solid 2/C Shielded Circuit Integrity Cable



1. Construction:

- 1.1. Conductors: 16 AWG (1.31 mm²) Bare Copper, 0.050" (1.27 mm) Nominal Diameter
- 1.2. Tape: Flame Retardant Tape
- 1.3. Insulation: Low Smoke Zero Halogen Thermoset Fire-Roc® 0.128" (3.25 mm) Nominal Diameter & 0.029" (0.73 mm) Nominal Wall Thickness
- 1.4. Color Code: Red, Black
- 1.5. Cable Assembly: Cable (2) Conductors Nominal 4.5" (114 mm) LHL Twist
- 1.6. Drain: 20 AWG (0.52 mm²) Stranded Bare Copper
- 1.7. Shield: Copper/Polyester Tape
- 1.8. Jacket: Non Halogen Flame Retardant Polyolefin Compound, Nominal Overall Diameter, 0.330" (8.38 mm), Nominal Wall Thickness 0.034" (0.15 mm) Color: RED
- 1.9. **Jacket Print:**
COMTRAN LSZH VITALink® FPLR-CI-LS CMR-CI-LS CL3R-CI-LS 2/C 16AWG SHLD 105C SUN RES WET FRR-2HR FOR USE IN FHIT SYSTEM 40A & FHIT7 SYSTEM 40A MAX VOLTAGE 72V ULC-S139 W/HOSE STREAM OR CSA FAS105 FT4 ST1 LL14444 PN35785 (MMYY) 000002 (01-12345)

NOTE: MMY is 4 Digit Month/Year
Sequential Footage Markings Every Two Feet

2. Compliance:

- 2.1. (UL) Listed Type FPLR-CI-LS
- 2.2. (UL) Listed Type CMR-CI-LS
- 2.3. (UL) Listed CL3R-CI-LS
- 2.4. CSA Listed FAS 105 FT4 ST1
- 2.5. UL Subject 1424 Power Limited Fire Alarm Circuits; 300V/105°C Classified
- 2.6. UL Subject 13 Power Limited Circuit Cables; 300V/105°C Classified
- 2.7. UL Subject 444 Communications Cable, 300V/105°C Classified
- 2.8. ANSI/UL 2196 2-Hour Fire Rating for use in FHIT System 40A
- 2.9. CAN/ULC-S139 2-Hour Fire Rating with Hose Stream for use in FHIT7 System 40A
- 2.10. NFPA 70 & 72
- 2.11. NFPA 130
- 2.12. NFPA 502
- 2.13. California State Fire Marshal Approved
- 2.14. NYC Electrical Advisory Board #54502, April 2017
- 2.15. RoHS Compliant

3. Physical Characteristics:

- 3.1. Nominal Conductor DCR @ 68F (20 °C): 4.09 Ω / 1000 Ft.
- 3.2. Nominal Weight per 1000 FT: 60 Lbs. (27.2 kg)
- 3.3. Min Bend Radius: 4" (101 mm)
- 3.4. Maximum Pull Tension – Straight runs: 41 Lbs. /Ft. (18.5 kg/Ft.)
- 3.5. Passes Cold Bend Test @ -20C

TITLE:		DESCRIPTION:	COMTRAN 330A Turner Street South Attleboro, MA 02703 Phone: 508-399-7004 Fax: 508-399-8839			 COMTRAN Innovative Systems. Engineered Solutions.  A Marmon Wire & Cable/Berkshire Hathaway Company
DS35785		16 AWG Solid 2 Conductor VITALink® Shielded Circuit Integrity Cable				
Rev	Date	Detail	Eng.	App.		
12	02/27/19	Add regulatory approvals	PB	WC		
11	01/08/19	Change logo and basic corrections	SM	WC		
10	10/31/18	Add LL # to print	PB	WC	ECN 18-118	
09	08/14/18	Added “Twist” to cable assembly description	PB	DG		
08	05/24/18	FAS from 90 to 105	PB	WC	ECN 18-067	
07	09/29/17	UPDATE LEGEND	PB	RN	ECN 17-100	
06	06/07/17	Additional listings add NYC EAB #	PB	RN		
05	6/15/16	Updated to include Canadian listings	PAB	RN		
04	05/02/16	Expanded Print with additional listings, expanded Compliance Section	PAB	RN		
03	10/8/15	Updated System number in print legend	PAB	RN		
02	9/10/15	Update to current format; add detail, electrical data	PAB	RN		
01	5/27/15	First Release	BAL	RN		

Comtran reserves the right to change the information above without prior notification. Comtran assumes no risk, and is not liable for direct or indirect, or consequential damages, resulting from the use of this document