


VITALink®

18 AWG 2-Conductor Shielded Circuit Integrity Cable



1. Construction:

- 1.1. Conductors: 18 AWG (0.82 mm²) Solid Bare Copper, 0.0403" (1.02 mm) Nominal Diameter
- 1.2. Tape: Flame Retardant Tape
- 1.3. Insulation: Low Smoke Zero Halogen Thermoset Fire-Roc® 0.118" (3.00 mm) Nominal Diameter & 0.029" (0.74 mm) Nominal Wall Thickness
- 1.4. Color Code: Red, Black
- 1.5. Cable Assembly: Cable (2) Conductors Nominal 4.25" (108 mm) LHL
- 1.6. Drain: 20 AWG (0.52 mm²) Stranded Bare Copper
- 1.7. Shield: Copper/Polyester Tape
- 1.8. Jacket: Non Halogen Flame Retardant Polyolefin Compound, Nominal Overall Diameter, 0.309" (7.85 mm), Nominal Wall Thickness 0.034" (0.86 mm) Color: RED

1.9. Jacket Print:

COMTRAN LSZH VITALink® FPLR-CI-LS CMR-CI-LS CL3R-CI-LS 2/C 18AWG SHLD 105C SUN RES WET FRR-2HR FOR USE IN FHIT SYSTEM 40A & FHIT7 SYSTEM 40A MAX VOLTAGE 72V ULC-S139 W/HOSE STREAM OR CSA FAS105 FT4 ST1 LL14444 PN36397 (MMYY) 000002 (01-12345)

NOTE: MMYY is 4 Digit Month/Year
Sequential Footage Markings Every Two Feet

2. Compliance:

- 2.1. (UL) Listed Type FPLR-CI-LS
- 2.2. (UL) Listed Type CMR-CI-LS
- 2.3. (UL) Listed CL3R-CI-LS
- 2.4. CSA Listed FAS 105 FT4 ST1
- 2.5. UL Subject 1424 Power Limited Fire Alarm Circuits; 300 V/105°C Classified
- 2.6. UL Subject 13 Power Limited Circuit Cables; 300V/105°C Classified
- 2.7. UL Subject 444 Communications Cable, 300V/105°C Classified
- 2.8. ANSI/UL 2196 2-Hour Fire Rating for use in FHIT System 40A
- 2.9. CAN/ULC-S139 2-Hour Fire Rating with Hose Stream for use in FHIT7 System 40A
- 2.10. NFPA 70 & 72
- 2.11. NFPA 130
- 2.12. NFPA 502
- 2.13. NYC Electrical Advisory Board #54502, April 2017
- 2.14. California State Fire Marshal Approved
- 2.15. RoHS Compliant

3. Physical Characteristics:

- 3.1. Nominal Conductor DCR @ 68F (20 °C): 6.51 Ω /1,000 Ft.
- 3.2. Nominal Weight per 1000 FT: 49 Lbs. (22.2 kg)
- 3.3. Min Bend Radius: 2" (50.8 mm)
- 3.4. Maximum Pull Tension – Straight runs: 26 Lbs. /Ft. (11.7 kg/Ft.)

TITLE:		DESCRIPTION:	COMTRAN 330A Turner Street South Attleboro, MA 02703 Phone: 508-399-7004 Fax: 508-399-8839		 COMTRAN Innovative Systems. Engineered Solutions.  A Marmon Wire & Cable/Berkshire Hathaway Company	
DS36397		18 AWG Shielded 2 Conductor VITALink® Circuit Integrity Cable				
Rev	Date	Detail	Eng.	App.		
08	02/27/19	Add regulatory approvals	PB	WC		
07	01/29/19	Change logo and basic corrections	SM	PB		
06	10/31/18	Add LL# to print	PB	WC	ECN 18/118	
05	10/30/18	Removed PLTC from text	PB	WC		
04	05/24/18	FAS 90 to 105	PB	WC	ECN 18-067	
03	10/05/17	Updated Legend	PB	RN		
02	06/07/17	Additional Listings add NYC EAB #	PB	RN		
01	05/10/97	First Release	PB	RN		

Comtran reserves the right to change the information above without prior notification. Comtran assumes no risk, and is not liable for direct or indirect, or consequential damages, resulting from the use of this document